Line Conditioner / AVR System

Automatic voltage regulator / Power conditioner / AC surge suppressor



Model #: LC2400

- Premium automatic voltage regulation (AVR), power conditioning and AC surge suppression
- Maintains regulated 120V nominal output over an input range of 89 to 147V
- 2400 watt / 20 amp capacity
- 4 NEMA 5-15R outlets, 2 NEMA 5-15/20R outlets, 6 foot AC cord
- LEDs display incoming voltage range, surge suppression and line fault status

DESCRIPTION

2400 watt Automatic Voltage Regulation (AVR) system. Protects sensitive electronics, computer accessories and home theater equipment from power-related damage and performance problems. Extends the useful life of connected equipment by providing optimum voltage conditions for enhanced efficiency and cooler internal operating temperatures. Reliable transformer-based voltage correction circuits maintain 120V nominal output during voltage fluctuations between 89 and 147V. Three levels of voltage stabilization offer targeted response for overvoltages, undervoltages and severe brownouts. Prevents equipment damage and power related performance problems for computer accessories, printers, home theater equipment, a/v components and other sensitive electronic devices. Network-grade AC surge and EMI/RFI noise suppression. Supports loads up to 2400 watts, 20A. Includes 6 AC outlets, 6 ft AC line cord and 7 diagnostic LEDs which display incoming voltage level, surge suppression status and line fault status.

KEY BUYING POINTS

- Maintains usable 120V (+10%/-12%) nominal output over an input range of 89 to 147V
- Protects sensitive electronics, computer accessories and home theater equipment from power-related damage and performance problems
- Extends the useful life of connected equipment by providing optimum voltage conditions for enhanced efficiency and cooler internal operating temperatures
- Three levels of voltage stabilization offer targeted response to overvoltages, undervoltages and severe brownouts
- Input voltages over 128V are reduced by 9.6%
- Input voltages between 103 and 112V are boosted by 8.9%
- Input voltages below 102V are boosted by 18.8%
- 2400 watts output power rating supports 120V loads up to 20 amps
- Network grade AC surge suppression
- Premium EMI/RFI noise filtering prevents equipment interaction, system interference, lockups and other power-related audio and video artifacts
- 7 diagnostic LEDs indicate input voltage levels, surge suppression status and line fault conditions
- 4 NEMA 5-15R & 2 NEMA 5-15/20R protected outlets
- 6 foot AC power cord with NEMA5-15P input plug

•

TYPICAL APPLICATIONS

• Maintains regulated output voltage during severe brownouts and overvoltages for computer accessories, printers, home theater equipment, a/v components, point-of-sale equipment, and other applications requiring clean, regulated AC power.

PACKAGE INCLUDES

- LC2400 Line Conditioner
- Instruction manual

COMPLETE SPECIFICATIONS

| OUTPUT | |
|--|---|
| Output watt capacity (watts): | 2400 |
| Output volt amp capacity (VA): | 2400 |
| Output nominal voltage: | 120V / 60Hz |
| Outlet quantity / type: | 4 NEMA5-15R and 2 NEMA5-20R (6 outlets total) |
| INPUT | |
| Input cord length (ft.): | 6.00 |
| Input cord length (m): | 1.83 |
| LEDS ALARMS & SWITCHES | |
| Front panel LEDs: | 7 LEDs show incoming voltage status, protection present and line fault conditions |
| SURGE / NOISE SUPPRESSION | |
| AC surge suppression: | 1440 joules |
| EMI / RFI AC noise suppression: | 75 dB |
| PHYSICAL | |
| Unit Dimensions (HWD/in): | 7.25 x 6 x 7 |
| Unit Dimensions (HWD/cm): | 18.4 x 15.2 x 17.8 |
| Form factors supported: | Small Tower |
| Material of construction: | Plastic |
| Shipping weight (lbs): | 12.2 |
| Shipping weight (kg): | 5.5 |
| WARRANTY | |
| Product warranty: | 2 years |
| Connected equipment insurance (USA and Canada Only): | |

The policy of Tripp Lite is one of continuous improvement.

Specifications are subject to change without notice.

Therefore, your product may vary slightly from what is currently listed.



Tripp Lite World Headquarters 1111 W. 35th Street Chicago, IL 60609 USA

> Customer Support (773) 869-1234

© 2004 Tripp Lite. All Rights Reserved.