







ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE
	B	ECN # 040716-1 CHANGE PACKING	07/16/04'
 *4	C	ECR # 080303-1 ADD ROHS,EDIT CONN,PACKING	03/03/08'
 *2	D	ECR # 080520-1 EDIT PACKING,ADD BARCODE NO.	05/20/08'



NOTE:

- HOOK UP WIRE : UL1007 18AWG COLOR:YELLOW, BLACK, RED
- CONNECTOR :
 P1 : 15 PIN SATA SOCKET CRIMP TYPE GOLD FLASH CONTACT 
 P2 : 4 PIN MATE LOCK MALE .
 HOUSING: JWT P/N: C5081H02-4P 
 TERMINAL: JWT P/N: C5081T0B-2 .

- HOOD: P1: MOLDED TYPE, PVC 45P, COLOR:BLACK(NK-K01)
- ELECTRICAL TEST: <1>100% OPEN SHORT & MIS WIRE TEST.
 <2>CONTACT RESISTANCE 3 Ohms MAX
 <3>INSULATION RESISTANCE 20M Ohms MIN

- PACKING: EACH PC / POLYBAG + HEADER CARD(FDRAG04)+P/N LABEL
 50 PCS / INNER CARTON WITH OUTER CARTON LABEL,
 INNER CARTON SIZE: 230*220*120mm,
 6 INNER CARTONS / MASTER CARTON,
 MASTER CARTON SIZE: 460*380*245mm.




 6.BAR CODE NO.: 7611990148547.

P1	P2
1, 2, 3	1
4, 5, 6	2
7, 8, 9	4
10, 11, 12	3

Tolerance	Inch	M/M
.X	.015	.30
.XX	.010	.10
.XXX	.005	.05

Rotronic Co., Ltd.

Title		SERIAL ATA POWER SUPPLY CABLE	
Draw		Customer P/N: 11.03.1055	
FANNIE 05/20/08'		App'd	
Check		Customer T-RAG	
Engr		Scale	NONE
		Units	m/m
		Third Angle Projection 	
		Dwg No.	150-0327
		REV:D	Sheet 1/1