

Switched Extension With Thermal Cut Out, 4 Gang

pro-ELEC



Specifications:

Plug Type	: UK
Connector Type A	: UK Plug
Connector Type B	: UK Mains Socket
Cable Assembly Type	: Power Cord
Current Rating	: 13A
Voltage Rating	: 250V AC
Cable Length	: 2m
Jacket Colour	: White
Standard	: BS 1363 : Part 2

Construction:

Item	Description	Material
1	Cover and Base	PP
2	Shutter	PA
3	L/N/E-Connection	Brass
4	Lamp Cover	PC
5	Switch	Outsourced
6	Thermal Overload	
7	Screw	Mild Steel
8	Spring	

Part Number Table

Description	Part Number
4 Way Extension Socket with Main Switch and thermal overload	2668-2M

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of the Group. © Premier Farnell plc 2012.

www.farnell.com
www.cpc.co.uk

pro-ELEC