


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [50079-8000](#)  
**Status:** **Active**  
**Overview:** [PicoBlade™](#)  
**Description:** 1.25mm Pitch PicoBlade™ Crimp Terminal, 26-28 AWG, Reel

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-51021-023 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-51021-024 (PDF)</a>
<a href="#">Product Specification PS-51021-001 (PDF)</a>	<a href="#">Product Specification PS-51021-025 (PDF)</a>
<a href="#">Product Specification PS-51021-002 (PDF)</a>	<a href="#">Product Specification PS-51021-026 (PDF)</a>
<a href="#">Product Specification PS-51021-009 (PDF)</a>	<a href="#">Product Specification PS-51021-027 (PDF)</a>
<a href="#">Product Specification PS-51021-010 (PDF)</a>	<a href="#">Product Specification PS-51021-028 (PDF)</a>
<a href="#">Product Specification PS-51021-011 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-51021-022 (PDF)</a>	



**General**

Product Family	Crimp Terminals
Series	<a href="#">50079</a>
Application	Signal
Crimp Quality Equipment	Yes
Overview	<a href="#">PicoBlade™</a>
Product Name	PicoBlade™
UPC	800753616233

**Physical**

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	10.100/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.50-1.04mm
Wire Size AWG	26, 28
Wire Size mm²	N/A

**Electrical**

Current - Maximum per Contact	1A
-------------------------------	----

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-51021-001, PS-51021-002, PS-51021-009, PS-51021-010, PS-51021-011, PS-51021-022, PS-51021-023, PS-51021-024, PS-51021-025, PS-51021-026, PS-51021-027, PS-51021-028, RPS-501576-001, RPS-51021-001, RPS-51021-002, RPS-51021-003, RPS-51021-004, RPS-51021-006, RPS-51021-007, RPS-51021-008, RPS-51021-010, RPS-51021-011, RPS-51021-013, RPS-51021-014, RPS-51021-015, RPS-51021-016, RPS-51021-017, RPS-51021-018, RPS-51021-021, RPS-51021-023, RPS-51021-024, RPS-51021-025, RPS-51021-026, RPS-51021-027, RPS-51021-028, RPS-51021-029,
-----------------------	--

<b>EU RoHS</b> <b>ELV and RoHS</b> <b>Compliant</b> <b>REACH SVHC</b> <b>Contains SVHC: No</b> <b>Low-Halogen Status</b> <b>Low-Halogen</b>	<b>China RoHS</b> 
---	--

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[50079Series](#)

**Mates With**

[50125 Crimp Terminal](#), [50133 Crimp Terminal](#)

**Use With**

[51021 Crimp Housing](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Extraction Tool	<a href="#">0011030043</a>
T2 Terminator	<a href="#">0639103700</a>
Tooling Die	
Hand Crimp Tool	<a href="#">0638110000</a>
Terminals on Metal Strip	

RPS-51021-030, RPS-51021-031, RPS-51021-032,  
RPS-51021-033, RPS-51021-034, RPS-51021-037,  
RPS-51021-038, RPS-51021-039, RPS-51021-040,  
RPS-51021-041, RPS-51021-043, RPS-51021-044,  
RPS-51021-045, RPS-51021-046, RPS-51021-047,  
RPS-51021-048, RPS-51021-050, RPS-51021-051,  
RPS-51021-052, RPS-51021-053, RPS-51021-054,  
RPS-51021-055, RPS-51021-056, RPS-51021-057,  
RPS-51021-058, RPS-51021-059, RPS-51021-060,  
RPS-51021-061, RPS-51021-062, RPS-51021-063,  
RPS-51021-064, RPS-51021-065, RPS-51021-066,  
RPS-51021-067, RPS-51021-068, RPS-51021-071,  
RPS-51021-072, RPS-51021-073, RPS-51021-074,  
RPS-51021-076, RPS-51021-077, RPS-51021-078,  
RPS-51021-079, RPS-51021-080, RPS-51021-083,  
RPS-51021-084, RPS-51021-085, RPS-51021-086,  
RPS-51021-089, RPS-51021-091, RPS-51021-092,  
RPS-51021-096, RPS-51021-097, RPS-51021-101,  
RPS-51021-102, RPS-51021-103, RPS-51021-104,  
RPS-51021-105, RPS-51021-106, RPS-51021-107,  
RPS-51021-108, RPS-51021-112, RPS-51021-113,  
RPS-51021-115, RPS-51021-117, RPS-53398-002,  
RPS-53398-037, RPS-53398-038  
SD-50079-001, SD-51021-002

Sales Drawing

Hand Crimp Tool for [0638190300](#)  
1.25mm Pitch Crimp  
Terminals, 26-32  
AWG Wire  
Hand Crimp Tool for [0638190400](#)  
1.25mm Pitch Crimp  
Terminals, 26-32  
AWG Wire  
FineAdjust™ [0639003700](#)  
1.25mm Pitch Crimp  
Terminal, 26-32  
AWG

Japan	
Description	Product #
Applicator for M21 1A Bench Press, 26-32 AWG Wire	<a href="#">0570673000</a>
Side-Feed Applicator For Full-Auto Machine	<a href="#">0570673200</a>
Extraction Tool	<a href="#">0570726000</a>

This document was generated on 01/09/2013

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**