





Product Details			
Model Name	LT	ECCO Group Europe Part Number	31105270
Description	BEACON, LT, XEN, 5W, MV, AMBER		
Product Type	Xenon Beacon	Application	Automotive / Industrial
Product Image – Amber beacon only shown		Product Dimensions	
			

Electrical Characteristics			
Input Voltage	10-100V DC, 20-72V AC	Input current	480mA @ 12V DC, 180mA @ 24V DC 92mA @ 48V DC, 77mA @ 60V DC 540mA @ 30V AC, 240mA @ 60V AC
Frequency	75 FPM	Light Source	Non-replaceable
Flash Mode	Single flash	Flash Pattern	N/A
Technology	Xenon	Power rating	5 W
		Estimated Tube Life	3,000 Hours
Other features	Reverse polarity protection		

Photometric Characteristics		Polar Plot
Colour	Amber	
Max intensity at HV0	12 cd	
Min intensity	12 cd	
Timing Diagram		

Enclosure			
IP rating	IP 67	Fixing centres	45 mm
Cable exit	Central base grommet	Fastening hardware	2 x M5 x 14mm studs with M5 nuts
Cable dimensions	2 x 0.75mm ²	Packaging	Thin wall carton
Recommended Mounting	Upright	Max Fastening Torque	3 N/m
Weight (unboxed)	130g	Weight (boxed)	150g

Approvals and Certifications			
EMC	UN ECE R10-03 6101	WEEE	Yes
CE	Yes	RoHS	Yes