

Produkt Informationen



WSD 81SE with country specific linecable

Bestellnummer : **T0053260811**



Soldering station PUD 81 includes soldering iron WP 65 and safety rest WDH 10 - country specific linecable included!

Technical data PUD 81

This station is ESD safe.



Dimensions L x B x H:	166 x 115 x 101 mm
Channels:	1
Power supply:	230 V
Power consumption:	80 W
Protection class:	1
Temperature range:	50°C - 450°C
Temperature accuracy:	+/- 9°C
Temperature stability:	+/- 5°C
Display:	LED
Setting via:	Buttons
Equipotential bonding:	Via 3,5 mm jack plug (normal state hard grounded)

- Easy handling
- Excellent cost / performance ratio
- Digital soldering station
- ESD safe

Technical data WP 65

Heating voltage:	24 V
Heating output:	65 W
Heat-up time:	approx. 7s from 50°C to 380°C
Temperature range:	50°C - 450°C
Tip type:	XNT

- Attractive soldering tip prices
- Optimized heat transfer due to solder tip sensor positioning
- Fast reaction time
- Excellent results on fine solder jobs with high heat demand