





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		A3	REVISED PER ECO-11-004835	11MAR11	RK	HMR

OBSOLETE	1.541	1.312	1.087	.971	.700	14	7	15	1658610-6
	1.216	.984	.759	.643	.400	8	BLACK	9	1658610-4
	1.541	1.312	1.087	.971	.700	14	BLACK	15	1658610-3
	2.090	1.852	1.623	1.511	1.200	24	BLACK	25	1658610-2
	2.732	2.500	2.275	2.159	1.800	36	BLACK	37	1658610-1
	F	E	D	C	B	A	HOUSING COLOR	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN B. MCMASTER	30MAR04	 TE Connectivity				
			CHK C. ROHDE	30MAR04					
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD M. WALMSLEY	30MAR04	NAME			
		0 PLC ± -		PRODUCT SPEC		RECPT ASSY, FRONT METAL SHELL, THREADED INSERTS, LEAD-FREE, AMPLIMITE HDF			
		1 PLC ± -		108-40012					
		2 PLC ± -		APPLICATION SPEC					
		3 PLC ± .005							
		4 PLC ± -		-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL		FINISH		WEIGHT -		A2	00779	C=1658610	-
				CUSTOMER DRAWING					
						SCALE	4:1	SHEET	1 of 2
						REV A3			

LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—



CONTACT DETAIL
SCALE 10:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MCMASTER 30MAR04	TE Connectivity				
		CHK C. ROHDE 30MAR04					
		APVD M. WALMSLEY 30MAR04	NAME				
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-40012			
		0 PLC ± -		APPLICATION SPEC			
		1 PLC ± -		—			
		2 PLC ± -		SIZE			
		3 PLC ± .005		CAGE CODE			
		4 PLC ± -		DRAWING NO			
		ANGLES ± 2°		RESTRICTED TO			
MATERIAL		FINISH		SCALE			
—		—		4:1			
		WEIGHT		SHEET			
		—		2 OF 2			
		CUSTOMER DRAWING		REV			
				A3			