



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		C1	REVISED PER ECO-11-004835	11MAR11	RK	HMR



1. CONNECTOR ACCEPTS SIZE 20 DF SOCKET CONTACTS, RETENTION TINES ARE AN INTEGRAL PART OF INSERT.
- 2 MATERIAL:
MOLDED PARTS – FLAME RETARDANT 94V-0 RATED, GLASS FILLED NYLON, BLACK.
SHELLS – STEEL PER ASTM A109.
- 3 FINISH:
SHELL – .000200 MIN TIN PLATE OVER .000100 MIN COPPER UNDERPLATE.
- 4 FINISH:
SHELL – ZINC PLATED .000200-.000400 THICK, YELLOW CHROMATE COATING.

STANDARD	4	.120	1658640-2
STANDARD	3	.120	1658640-1
PACKAGING TYPE	FINISH	DIM A	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.REITZEL 29 JUL 03	 TE Connectivity				
		CHK S.BOLASH 29 JUL 03					
DIMENSIONS: INCHES		APVD M.WALMSLEY 29 JUL 03	NAME RECEPTACLE CONNECTOR, SIZE 5, 50 POS., AMPLIMITE HDP —				
		PRODUCT SPEC 108-40005					
		APPLICATION SPEC 114-40030					
MATERIAL		WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C-1658640	RESTRICTED TO —	
		FINISH SEE TABLE	CUSTOMER DRAWING				
			SCALE 4:1	SHEET 1 of 1	REV C1		