

Uncontrolled document as of February 20, 2013. Refer to website for up to date specifications.



Submersible

### MityLite™ 1900 Flashlight

Unlike conventional flashlights that have a yellowish beam, the MityLite 1900 flashlight uses a hi-intensity Xenon lamp that produces a powerful, bright beam. Use this compact flashlight to cut through thick smoke, fog, and dust. It is submersible and comes with a twist-on shroud. The 1900 is ideal for any situation. Powered by 2 AAA alkaline cells.

Body Material: Xenoy Polymer Resin

Minimum Pack 6 ea.

Package Weight: 2.4 oz.

### MityLite™ 1900 Flashlight Specifications

	High	
<b>LIGHT SOURCE</b>	Xenon	
<b>BATTERIES</b>	2 AAA Alkaline (Included)	
<b>CHARGE TIME</b>	N/A	
<b>VOLTAGE</b>	3	
<b>LENGTH</b>	4.09" (10.4 cm)	
<b>WEIGHT w/ BATTERIES</b>	1.6 oz. (0.05 kg)	
<b>WEIGHT w/o BATTERIES</b>	0.75 oz. (0.02 kg)	

### MityLite™ 1900 Flashlight Configurations

Cat. #	Description
1900	MityLite™ 1900 Flashlight (Carded)
1900T	MityLite™ 1900 Flashlight (Clear Gift Tube)
1900M	MityLite™ 1900 Flashlight Merchandiser Display

### NSN List

NSN #	Description
6230-01-518-2061	1900TNVG Black
6230-01-365-7647	1900T Orange
6230-01-324-2950	1900T Orange
6240-01-428-9410	1904 Lamp Module
6230-01-463-8505	1900C
6230-01-281-3774	1900LM
6230-01-345-6314	1900T Black
6230-01-522-3357	1900C Yellow

### MityLite™ 1900 Flashlight Accessories

Cat. #	Description
722	Helmet Light Holder
1904	MityLite™ 1900 Lamp Module

	FL1 STANDARD	High	
<b>LIGHT OUTPUT</b>		11 LUMENS	
<b>RUNTIME (hours/min)</b>		1h 30m	
<b>BEAM DISTANCE (meters)</b>		45m	
<b>PEAK BEAM INTENSITY (candela)</b>		571cd	
<b>WATERPROOF &amp; SUBMERSIBLE</b>		IPX7	IPX7

### MityLite™ 1900 Flashlight Approvals



Class I, Div. 2; Gp ABCD, T3C; Class II; Div. 2; Gp G.

---



Ex ib e IIC T4 IP67 IEC Ex TSA 06.0021X

---



Class I, Div. 1, GP C,D, T3C CONFORMS TO STD UL 783

---

**Pelican Products, Inc.**

23215 Early Avenue • Torrance, CA 90505 • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311  
e-mail: [CSR.Consumer@pelican.com](mailto:CSR.Consumer@pelican.com) • [www.pelican.com](http://www.pelican.com)