

Uncontrolled document as of February 20, 2013. Refer to website for up to date specifications.

LIGHTS
2430
MityLite



MityLite™ 2430 Flashlight

The compact design of the 2430 Flashlight makes it perfect for general use, around the house or at work. The contoured ABS body is corrosion proof and virtually indestructible. It comes with a push button tail switch for one hand operation. For hands-free use, attach it to your helmet or hard hat with clip included. The MityLite 2430 is powered by 4 AA alkaline cells, also included.

Body Material: ABS Resin
Minimum Pack 6 ea.
Packaged Weight: 8.0 oz.

MityLite™ 2430 Flashlight Specifications

High	
LIGHT SOURCE	Xenon
BATTERIES	4 AA Alkaline (Included)
CHARGE TIME	N/A
VOLTAGE	6
LENGTH	6.5" (16.5 cm)
WEIGHT w/ BATTERIES	6.1 oz. (0.17 kg)
WEIGHT w/o BATTERIES	2.6 oz. (0.07 kg)

MityLite™ 2430 Flashlight Configurations

Cat. #	Description
2430	MityLite™ 2430 Flashlight (Carded)

MityLite™ 2430 Flashlight Accessories

Cat. #	Description
700	Helmet Light Holder
710	Helmet Light Holder
711	Helmet Light Holder
712	Helmet Light Holder
750	Helmet Light Holder
760	Helmet Light Holder
770	Universal Helmet Light Holder
2424	MityLite™ 2430 Xenon Lamp Module

FL1 STANDARD		High	
LIGHT OUTPUT		70 LUMENS	
RUNTIME (hours/min)		2h 15m	
BEAM DISTANCE (meters)		104m	
PEAK BEAM INTENSITY (candela)		2766 cd	
WATER RESISTANT		IPX4	IPX4

MityLite™ 2430 Flashlight Approvals



Listed 4S67/E184884 Class I, Div. 2; Gp.C, D T2A (265Å°)

Pelican Products, Inc.

23215 Early Avenue • Torrance, CA 90505 • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
e-mail:CSR.Consumer@pelican.com • www.pelican.com