

Uncontrolled document as of February 20, 2013. Refer to website for up to date specifications.

LIGHTS
1800
PeliLite



Submersible

PeliLite™ 1800 Flashlight

This one is built to last. The unbreakable ABS body resists chemicals, water and corrosion. The polycarbonate lens and focused Xenon lamp module produce a tight white beam that penetrates smoke and fog. The PeliLite 1800 flashlight is submersible, thanks to the o-ring seal and twist-on shroud that eliminates leaky switches. It is powered by 2 C alkaline cells.

Body Material: ABS Resin
Minimum Pack 6 ea.
Packaged Weight: 3.8 oz.

PeliLite™ 1800 Flashlight Specifications

	High	
LIGHT SOURCE	Xenon	
BATTERIES	2 C Alkaline (Not included)	
CHARGE TIME	N/A	
VOLTAGE	3	
LENGTH	6" (15.2 cm)	
WEIGHT w/ BATTERIES	7.8 oz. (0.22 kg)	
WEIGHT w/o BATTERIES	2.9 oz. (0.08 kg)	

PeliLite™ 1800 Flashlight Configurations

Cat. #	Description
1800	PeliLite™ 1800 Flashlight (Carded)

NSN List

NSN #	Description
6230-01-365-7648	1800 Orange
6230-01-465-5045	1800C Black

PeliLite™ 1800 Flashlight Accessories

Cat. #	Description
1804	PeliLite™ 1800 Xenon Lamp Module

	FL 1 STANDARD	High	
LIGHT OUTPUT		21 LUMENS	
RUNTIME (hours/min)		7h	
BEAM DISTANCE (meters)		131m	
PEAK BEAM INTENSITY (candela)		4370 cd	
WATERPROOF & SUBMERSIBLE		IPX7	IPX7

PeliLite™ 1800 Flashlight Approvals



Class I, Div. 2; Gp ABCD, T3C / Class II; Div. 2; Gp G.



Class I, Div. 2; Gp. ABCD / Class II; Div. 2; Gp. G; T4



Listed 4S67/E184884 Class I, Div. 2; Gp. D / Class I; Zone 2; Gp. IIA; T3

Pelican Products, Inc.

23215 Early Avenue • Torrance, CA 90505 • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
e-mail: CSR.Consumer@pelican.com • www.pelican.com