



datasheet for KLEPS 30  
 article number: 930113101



<b>product description:</b>	order number: 930 113-101
<b>description:</b>	Clamp-type test probe with rotating grip jaws and flexible shaft. The special form of the grip jaws allows clamping of pins and wires up to a maximum of 4mm diameter. 4mm diameter brass socket connection with side screw, grip jaws additionally tin-plated.
<b>typ:</b>	KLEPS 30 rot / red
<b>system:</b>	4mm system
<b>order number:</b>	930 113-101
<b>clamping range:</b>	4 mm
<b>clamping typ:</b>	rotating grip jaws
<b>color</b>	
<b>other color versions:</b>	
<b>technical data</b>	
<b>measurement category acc. to IEC 61010:</b>	CAT I
<b>norm</b>	IEC 61010
<b>type of termination:</b>	4 mm socket (unsprung) screw
<b>rated voltage:</b>	30 VAC / 60 VDC
<b>rated current:</b>	4 A
<a href="#">Please consider derating curve!</a>	
<b>contact resistance:</b>	10 mOhm
<b>material</b>	
<b>contact material:</b>	grip jaws: spring steel socket: brass
<b>contact surface material:</b>	grip jaws: tin
<b>housing material:</b>	PF
<b>environmental conditions:</b>	
<b>temperature range:</b>	-25 °C to +80 °C
<b>inflammable class:</b>	
<b>housing (basic material):</b>	UL 94 V - 0
<b>drawing</b>	

