



RBK HSS JOBBER DRILL 10.20MM

DIN 338/BS 328

Flute Geometry Standard Helix, right hand spiral

Surface finish Blue

Point geometry Up to 2.9mm - 118° 3.0mm and above - 135° split point

Angle, drill point	118 °
Diameter, External	10.20 mm
Length, effective	87 mm
Length, overall	133 mm
Material	HSS
RoHS Compliant	NA