



72-9280 SPECIFICATIONS

Basic Functions	Range	Best Accuracy
DC Voltage	4V/40V/400V/1000V	±(0.5%+ 3)
AC Voltage	4V/40V/400V/1000V	±(1%+ 3)
DC Millivoltage	40mV/400mV	±(0.8%+ 3)
DC Current	400μA/4000μA/40mA/400mA/4A/10A	±(1%+ 2)
AC Current	400μA/4000μA/40mA/400mA/4A/10A	±(1.2%+ 5)
Resistance	400Ω/4KΩ/40KΩ/400KΩ/4MΩ/40MΩ	±(1%+ 5)
Capacitance	10nF/100nF/1000nF/10μF/100μF	±(3%+ 5)
Frequency	10Hz - 1MHz	±(0.1%+ 4)
Special Functions		
Auto Ranging		✓
Dwell	4Cyl / 6Cyl / 8Cyl	±(3%+ 5)
Tach	4Cyl / 6Cyl / 8Cyl	±(3%+ 5)
Diode		✓
Continuity Buzzer		✓
Max / Min Mode		✓
Data Hold		✓
Sleep Mode		✓
Display Backlight		✓
RS232 (USB)		✓
Low Battery Display		✓
Input Impedance for DC Voltage Measurement	≥ 10MΩ	✓
Max. Display	3999	✓
GENERAL CHARACTERISTICS		
Power	9V Battery (6F22)	
LCD Size	65 x 43mm	
Product Colour	Orange and Grey	
Product Net Weight	362g	
Product Size	180 x 87 x 47mm	
Standard Accessories	Test Lead, Battery, English Manual, RS232 Interface Cable, Software, Alligator Clip	
Optional Accessories*	USB Interface Cable	
Standard Individual Packing	Gift Box	
Standard Quantity Per Carton	20pcs	
Standard Carton Measurement	465 x 335 x 345mm (0.054 CBM Per Export Carton)	
Standard Carton Gross Weight	15kg	

* Specifications and other information are subject to change without further