


U.I. Lapp GmbH	<b>PRODUCT INFORMATION</b>	
	<b>SKINDICHT® BL-M</b>	<b>12.09.2012</b>

For closing pre-threaded holes  
Assembling with screwdriver



### Application range

Machine and equipment manufacturing  
Electric motor manufacturing

### Design

Metric connection thread acc. to EN 50262

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

### Technical Data


On request:	Fitted with FKM O-ring
Material:	Body: nickel-plated brass Sea water-resistant
Protection rating:	IP 54 IP 68 with O-ring
Temperature range:	With O-ring: -30°C to +100°C Without O-ring: -60°C to +200°C

Product Management	Document: LAPP_PRO1029EN.pdf	1 / 3
--------------------	------------------------------	-------

## SKINDICHT® BL-M

12.09.2012

Part number	Article designation / size	Outer Ø (mm)	Pieces / PU
SKINDICHT® BL-M			
52103100	12 x 1,5	14.0	100
52103110	16 x 1,5	18.0	100
52103120	20 x 1,5	22.0	100
52103130	25 x 1,5	28.0	100
52103140	32 x 1,5	35.0	50
52103150	40 x 1,5	44.0	25
52103160	50 x 1,5	54.0	10
52103170	63 x 1,5	70.0	10
SKINDICHT® BL-M with O-ring			
52103105	12 x 1,5	14.0	100
52103115	16 x 1,5	18.0	100
52103125	20 x 1,5	22.0	100
52103135	25 x 1,5	28.0	100
52103145	32 x 1,5	35.0	50
52103155	40 x 1,5	44.0	25
52103165	50 x 1,5	54.0	10
52103175	63 x 1,5	70.0	10
52103190	75 x 1,5	80.0	1

U.I. Lapp GmbH	<b>PRODUCT INFORMATION</b>	 <b>LAPP GROUP</b>
	<b>SKINDICHT® BL-M</b>	<b>12.09.2012</b>



Product Management	Document: LAPP_PRO1029EN.pdf	3 / 3
--------------------	------------------------------	-------