Pressure washers **K 4 Compact**



The new powerful K4 Compact is small, easy to transport and is ideal for all cleaning tasks around the home. Complete with a vario power lance and Kärcher's long life water-cooled motor.

Standard accessories:

- Integrated fine mesh water filter
- Adapter garden hose A3/4"
- High-pressure hose 6 m
- Detergent suction hose With filter
- Plug 'n' Clean System
- Gun with quick connect
- Water cooled engine
- Vario-power spray lance
- Dirt Blaster
- 1 L RM 555 universal cleaner

Order no.: 1.637-311.0



Technical data

Pressure (bar/MPa)	20-up to 130/2-up to 13
Flow rate I/h	max. 420
Area performance (m²/h)	30
Max. water feed temperature (°C)	max. 40
Power rating (kW)	1.8
Power	-
Weight without access. (kg)	14.1
Dimensions (L x W x H) (mm)	349x426x878
Detergent tank	-
Frequency Hz	50
Voltage V	230

Details

Description

The K4 Compact Pressure Washer combines power & energy efficiency and is equipped with an innovative water-cooled induction motor for enhanced performance and longer life. In addition the Quick Connect hose system eliminates kinking and reduces set up times making it even easier to use. Compact dimensions allow for convenient transportation and storage. The aluminium telescopic handle

and wheels makes this machine easy to use and ensures excellent mobility. Ideal for cleaning all around the home, the K4 Compact includes a vario lance, detergent suction hose

and dirtblaster lance which provides up to 50% greater cleaning power than a standard high pressure lance.

An impact-resistant recyclable plastic casing and fine mesh water filter prevent dirt particles from damaging the motor and three-piston axial-flow pump, whilst a safety valve prevents pressure overload. All Karcher K4, K5 & K7 Pressure washers can work using a static or harvested water source such as a water butt. Water can either be drawn using a Karcher suction hose & filter or connected to a water butt tap.

The K4 Compact comes with a 3 year guarantee.

Features & Benefits

Easy to transport

The small, robust devices in the Compact series have two carrying handles and can easily be taken with you, wherever you go. These practical, compact devices can be stored quickly and easily, even in the boot of a car, and take up minimal space.

Outstanding performance

The state-of-the-art water-cooled motor will impress you with its long service life and high level of performance.

Quick Connect

The high-pressure hose is easy to manoeuvre, clicking quickly in and out of the device and gun. This saves time and effort.

Clean tank solution

All Kärcher high-pressure cleaner equipment includes an integrated suction mechanism for cleaning agents.

Accessories

Accessory kits

Window and conservatory cleaning set

Window and conservatory cleaning set includes soft flat brush, vario joint, 3-stage lance extension and squeegee. For cleaning and drying windows and conservatories.

Order no. 2.640-771.0

Brushes and cleaning sponges

Universal soft brush

Universal soft brush for cleaning all types of surfaces. With soft brushes, outer protector ring, union nut and rubber pad.

Order no. 2.640-589.0

Soft brush

Order no. 2.640-590.0

Rotating wash brush with joint

Rotating washing brush with joint for cleaning all smooth surfaces, e.g. paint, glass or plastic. 18° infinitely adjustable joint on handle for cleaning difficult to reach areas.

Order no. 2.640-907.0

Wheel wash brush

Wheel wash brush for effective cleaning also in difficult to reach areas. Uniform 360° water distribution for a perfect cleaning result.


Order no. 2.640-699.0

Hard surface cleaners

T 300 "T-Racer" surface and patio cleaner

T 300 T-Racer. For cleaning flat surfaces without splash back. Additional handle for vertical surfaces. Features two rotating flat jet nozzles. Hovercraft effect. Distance of nozzle to surface adjustable.

Order no. 2.640-212.0














Soft brush for cleaning large areas, e.g. cars, caravans, boats, conservatories or roller shutters). Working width of 248 mm ensures good coverage.

Hard surface cleaners

Delta-Racer D 150 packaged

Delta-Racer D 150 for cleaning sensitive surfaces without splash back. Efficient combination of high pressure and manual brush pressure saves energy, water and up to 30% time.

Order no. 2.641-812.0

PS 40 power scrubber

PS 40 power scrubber with three integrated high-pressure nozzles. Powerful cleaning action removes stubborn dirt from surfaces guickly and easily. Ideal for stairs and edges.

Order no. 2.640-865.0

T-Racer replacement nozzles, grey, K2 – K5

High-quality, grey replacement nozzles for T-Racer nozzles. Suitable for nozzle replacement for K2 – K5 series (T 250, T 300, T 400).

Order no. 2.640-727.0

High-pressure hose extension - System from 2008

High-pressure extension hose, 6 m, K3 - K7 (for gun model "Best"). High-pressure extension hose for greater flexibility. 6 m robust DN 8 quality hose for durability. For K3 – K7 series from 2008 with Quick Connect connector.

Order no. 2.641-709.0

High-pressure extension hose, 10 m, K3 - K7 (for gun model "Best"). High-pressure extension hose for greater flexibility. 10 m robust DN 8 quality hose for durability. For K3 – K7 series from 2008 with Quick Connect connector.

Order no. 2.641-710.0

High-pressure extension rubber hose, 10 m, K5 - K7 (for gun model "Best").

High-pressure extension rubber hose for greater flexibility. 10 m high-guality hose, steel reinforced for durability. For K5 - K7 series from 2008 with Quick Connect connector.

Order no. 2.641-708.0

High-pressure hose extension - System from 2009

High-pressure replacement hose, 9 m, K3 - K7

9 m high-pressure replacement hose for K3 - K7 series domestic pressure washers from 2009, where the hose is connected to the gun and pressure washer per Quick Connect connector, 160 bar, 60 °C.

Order no. 2.641-721.0















High-pressure hose extension - System up to 2007

High-pressure extension rubber hose, 10 m, K2 - K8. High-pressure extension rubber hose for greater flexibility. 10 m high-quality rubber hose, steel reinforced for durability. Temperature: up to 80 °C. Pressure: up to 160 bar.

Order no. 6.390-096.0

High-pressure hose replacement kit - from 1992

Accessories kit quick connect *UK

Order no. 2.642-301.0

Hoses & Hose Reels/Trolleys

Connection Set for high-pressure cleaners

Hose set for high pressure cleaning or for watering the garden. With 10 m PrimoFlex®-hose (3/4"), G3/4-tap adapter, 1 x Universal hose connector as well as Universal hose connector with Aqua Stop.

Order no. 2.645-156.0

Miscellaneous

Water filter

Water filter protects pressure washer pumps against dirt particles from dirty water.

Order no. 4.730-059.0

Spare fine filter element

Three spare fine filter elements for replacing fine water filters of Kärcher highpressure cleaners.

Order no. 4.730-108.0

Adapter for garden hose connection

Order no. 2.640-732.0

Special applications

Pipe cleaning set, 7.5 m

Pipe cleaning set with 7.5 m hose for clearing blockages in pipes, drains, downpipes and toilets.

Order no. 2.637-729.0















Special applications

Replacement O-ring set

Replacement O-ring set for easy replacement of O-rings and safety plugs for pressure washer accessories.

Order no. 2.640-729.0

Suction hose with check valve

Suction hose with check valve Pumps water from ponds or water butts for pressure washer use. No further water connection necessary.

Order no. 4.440-238.0

Pipe cleaning set with 15 m hose for clearing blockages in pipes, drains, downpipes and toilets.

Order no. 2.637-767.0

Pipe cleaning set, 15 m

Sand/wet blasting set

Sand and wet blasting set for removing rust, paint and stubborn dirt using Kärcher abrasive.

Order no. 2.638-792.0

Vario joint

Vario joint, rotates 180° for cleaning difficult to reach areas. Connection: For connection between gun and accessory or extension lance and accessory.

Order no. 2.640-733.0

Foam nozzle, 0.3 litre

Order no. 2.641-848.0

Foam nozzle, 0.6 litre

Foam nozzle with powerful foam effortlessly cleans all types of surfaces, e.g. car or motorcycle paint, glass or stone, 0.6 litre container.

Foam nozzle with powerful foam effortlessly cleans all types of surfaces, e.g. car

or motorcycle paint, glass or stone, 0.3 litre container.

Order no. 2.641-847.0

















Special applications

Roof gutter and pipe cleaning set Order no. 2.642-240.0

Suction hose ecologic Order no. 2.642-743.0

Spray lances

Order no. 2.642-739.0

Vario-Power spray lance, K3 – K4

Under Chassis Cleaner *GB

Vario-Power spray lance: spray lance with infinitely variable pressure control from low-pressure detergent jet to high-pressure jet.

Highly effective underbody cleaner for effortless removal of dirt, sludge, mud,

sand and salt deposits. Includes nozzle for applying underbody wax.

Order no. 4.760-565.0

Dirt blaster, K2 – K4 Dirt blaster with powerful rotor nozzle (rotating pencil jet) ideal for removing stubborn dirt. Ideal for moss covered or weathered surfaces.

Order no. 4.763-977.0

Triple nozzle lance Triple nozzle lance with three types of jets: High-pressure fan jet, high-pressure pencil jet and low-pressure chemical jet.

Order no. 4.760-269.0











Spray lances

Splash guard for dirt blaster

Splash guard for dirt blasterProtects against splash back when cleaning corners and edges. Fits all Kärcher dirt blasters (except 4.763-184).

Order no. 2.640-916.0

Angled spray lance

Extra-long angled spray lance (about 1 m) for easy cleaning of difficult to reach areas, e.g. roof gutters or vehicle underbodies.

Order no. 2.638-817.0

Extension lance

Extends spray lance by 0.4 m. For effective cleaning of difficult to reach areas. Suitable for all Kärcher accessories.

Order no. 4.760-262.0

Flexible spray lance

Flexible spray lance with adjustable high and low-pressure jet. Adjustable spray lance rotates through 180° for easier cleaning of difficult to reach areas.

Order no. 4.760-272.0

3-stage lance extension

3-stage lance extension set with four aluminium lances for difficult to reach areas. Variable extension to 90 cm, 1.30 m and 1.70 m.

Order no. 2.639-722.0

Multi-Power-Jet K3 -K5 Order no. 2.642-440.0

Telescopic jet pipe Order no. 2.642-347.0

















