

K 2 Compact Car

Compact & lightweight, the K2 Compact Car pressure washer is ideal for all cleaning tasks around the home and includes a Car kit with wash brush, 0.3 l foam nozzle and car shampoo.

Standard accessories:

- Car kit
- Integrated fine mesh water filter
- Adapter garden hose A3/4"
- Trigger gun
- High-pressure hose 4 m
- Detergent suction hose With filter
- One-way spray lance
- Dirt Blaster



Order no.: 1.673-129.0

Technical data

Pressure (bar/MPa)	max. 110/max. 11
Flow rate l/h	max. 360
Area performance (m ² /h)	20
Max. water feed temperature (°C)	max. 40
Power rating (kW)	1.4
Power	-
Weight without access. (kg)	4
Dimensions (L x W x H) (mm)	280x176x443
Detergent tank	-
Frequency (Hz)	50-60
Voltage (V)	220-240

Details

Description

Compact & lightweight, the K2 Compact Car pressure washer is easy to transport and is ideal for all cleaning tasks around the home. Included with the machine is a trigger gun, 4m high pressure hose, one way lance, detergent suction facility and a dirtblaster lance which provides up to 50% greater cleaning power than a standard high pressure lance. The K2 Compact Car also comes complete with a Car kit containing a wash brush, foamer and car shampoo.

A pressure switch control switches the motor on and off when the ergonomically-designed trigger gun is pressed and released, whilst an impact-resistant, recyclable plastic casing effectively prevents dirt particles from damaging the motor and pump.

All Kärcher K2 Pressure Washers can also be used from a gravity fed harvested water source such as a water butt tap.

The K2 Compact comes with a 2 year guarantee.

Features & Benefits

Tidy storage on the hook

Generous cable hooks allow tidy storage of the cable directly on the device.

Full cleaning power

All Kärcher high-pressure cleaner equipment includes an integrated suction mechanism for cleaning agents.

Sits comfortably in the hand

Thanks to the ergonomic carrying handle and the low weight, the device is light and easy to transport.

Accessories

Brushes and cleaning sponges

Universal soft brush

Universal soft brush for cleaning all types of surfaces. With soft brushes, outer protector ring, union nut and rubber pad.

Order no. 2.640-589.0



Soft brush

Soft brush for cleaning large areas, e.g. cars, caravans, boats, conservatories or roller shutters). Working width of 248 mm ensures good coverage.

Order no. 2.640-590.0



Rotating wash brush with joint

Rotating washing brush with joint for cleaning all smooth surfaces, e.g. paint, glass or plastic. 18° infinitely adjustable joint on handle for cleaning difficult to reach areas.

Order no. 2.640-907.0



Wheel wash brush

Wheel wash brush for effective cleaning also in difficult to reach areas. Uniform 360° water distribution for a perfect cleaning result.

Order no. 2.640-699.0



Hard surface cleaners

T 300 "T-Racer" surface and patio cleaner

T 300 T-Racer. For cleaning flat surfaces without splash back. Additional handle for vertical surfaces. Features two rotating flat jet nozzles. Hovercraft effect. Distance of nozzle to surface adjustable.

Order no. 2.640-212.0



Delta-Racer D 150 packaged

Delta-Racer D 150 for cleaning sensitive surfaces without splash back. Efficient combination of high pressure and manual brush pressure saves energy, water and up to 30% time.

Order no. 2.641-812.0



Hard surface cleaners

PS 40 power scrubber

PS 40 power scrubber with three integrated high-pressure nozzles. Powerful cleaning action removes stubborn dirt from surfaces quickly and easily. Ideal for stairs and edges.

Order no. 2.640-865.0



T-Racer replacement nozzles, grey, K2 – K5

High-quality, grey replacement nozzles for T-Racer nozzles. Suitable for nozzle replacement for K2 – K5 series (T 250, T 300, T 400).

Order no. 2.640-727.0



High-pressure hose extension - System from 2008

High-pressure extension rubber hose, 10 m, K5 - K7 (for gun model "Best").

High-pressure extension rubber hose for greater flexibility. 10 m high-quality hose, steel reinforced for durability. For K5 – K7 series from 2008 with Quick Connect connector.

Order no. 2.641-708.0



High-pressure hose extension - System up to 2007

High-pressure extension hose, 6 m, K2 - K7

High-pressure extension hose for greater flexibility, 6 m robust DN 8 quality hose. Textile braiding reinforced, non-kinking hose with brass connector for durability.

Order no. 6.390-243.0



High-pressure extension hose, 10 m, K2 - K7

High-pressure extension hose for greater flexibility, 10 m robust DN 8 quality hose. Textile braiding reinforced, non-kinking hose with brass connector for durability.

Order no. 6.389-092.0



High-pressure extension hose, 10 m, K2 - K7

High-pressure extension hose for greater flexibility, 10 m robust DN 8 quality hose. Textile braiding reinforced, non-kinking hose with brass connector for durability.

Order no. 6.390-961.0



High-pressure hose extension - System up to 2007

High-pressure extension rubber hose, 10 m, K2 - K8.

High-pressure extension rubber hose for greater flexibility. 10 m high-quality rubber hose, steel reinforced for durability. Temperature: up to 80 °C. Pressure: up to 160 bar.

Order no. 6.390-096.0



High-pressure hose replacement kit - from 1992

Accessories kit quick connect *UK

Order no. 2.642-301.0



Hoses & Hose Reels/Trolleys

Connection Set for high-pressure cleaners

Hose set for high pressure cleaning or for watering the garden. With 10 m PrimoFlex®-hose (3/4"), G3/4-tap adapter, 1 x Universal hose connector as well as Universal hose connector with Aqua Stop.

Order no. 2.645-156.0



Miscellaneous

Replacement gun model "Good"

Replacement gun for Kärcher K2 – K7 series domestic pressure washers. For all pressure washers where the hose is secured to the gun with a clip (without Quick Connect).

Order no. 2.641-959.0



Water filter

Water filter protects pressure washer pumps against dirt particles from dirty water.

Order no. 4.730-059.0



Spare fine filter element

Three spare fine filter elements for replacing fine water filters of Kärcher high-pressure cleaners.

Order no. 4.730-108.0



Adapter for garden hose connection

Order no. 2.640-732.0



Special applications

Pipe cleaning set, 7.5 m

Pipe cleaning set with 7.5 m hose for clearing blockages in pipes, drains, downpipes and toilets.

Order no. 2.637-729.0



Replacement O-ring set

Replacement O-ring set for easy replacement of O-rings and safety plugs for pressure washer accessories.

Order no. 2.640-729.0



Pipe cleaning set, 15 m

Pipe cleaning set with 15 m hose for clearing blockages in pipes, drains, downpipes and toilets.

Order no. 2.637-767.0



Sand/wet blasting set

Sand and wet blasting set for removing rust, paint and stubborn dirt using Kärcher abrasive.

Order no. 2.638-792.0



Vario joint

Vario joint, rotates 180° for cleaning difficult to reach areas. Connection: For connection between gun and accessory or extension lance and accessory.

Order no. 2.640-733.0



Foam nozzle, 0.3 litre

Foam nozzle with powerful foam effortlessly cleans all types of surfaces, e.g. car or motorcycle paint, glass or stone, 0.3 litre container.

Order no. 2.641-848.0



Foam nozzle, 0.6 litre

Foam nozzle with powerful foam effortlessly cleans all types of surfaces, e.g. car or motorcycle paint, glass or stone, 0.6 litre container.

Order no. 2.641-847.0



Special applications

Roof gutter and pipe cleaning set

Order no. 2.642-240.0



Under Chassis Cleaner *GB

Highly effective underbody cleaner for effortless removal of dirt, sludge, mud, sand and salt deposits. Includes nozzle for applying underbody wax.

Order no. 2.642-739.0



Spray lances

Dirt blaster, K2 – K4

Dirt blaster with powerful rotor nozzle (rotating pencil jet) ideal for removing stubborn dirt. Ideal for moss covered or weathered surfaces.

Order no. 4.763-977.0



Vario-Power spray lance, K2

Vario-Power spray lance: spray lance with infinitely variable pressure control from low-pressure detergent jet to high-pressure jet.

Order no. 4.760-543.0



Triple nozzle lance

Triple nozzle lance with three types of jets: High-pressure fan jet, high-pressure pencil jet and low-pressure chemical jet.

Order no. 4.760-269.0



Splash guard for dirt blaster

Splash guard for dirt blasterProtects against splash back when cleaning corners and edges. Fits all Kärcher dirt blasters (except 4.763-184).

Order no. 2.640-916.0



Spray lances

Angled spray lance

Extra-long angled spray lance (about 1 m) for easy cleaning of difficult to reach areas, e.g. roof gutters or vehicle underbodies.

Order no. 2.638-817.0



Extension lance

Extends spray lance by 0.4 m. For effective cleaning of difficult to reach areas. Suitable for all Kärcher accessories.

Order no. 4.760-262.0



Flexible spray lance

Flexible spray lance with adjustable high and low-pressure jet. Adjustable spray lance rotates through 180° for easier cleaning of difficult to reach areas.

Order no. 4.760-272.0



3-stage lance extension

3-stage lance extension set with four aluminium lances for difficult to reach areas. Variable extension to 90 cm, 1.30 m and 1.70 m.

Order no. 2.639-722.0



Telescopic jet pipe

Order no. 2.642-347.0

