

Cold water compact class

HD 5/12 C Plus



Compact versatile high performance pressure cleaner

Standard accessories:

- Trigger gun : extended
- Easy Press
- Trigger gun with soft grip
- High-pressure hose 10 m
- Spray lance 550 mm
- Triple nozzle (0°/25°/40°)
- Dirt Blaster
- Anti-twist system (AVS)
- Pressure switch control

Order no.: 1.514-103.0



Technical data

Current type Ph/V/Hz	1/240/50
Flow rate l/h	500
Operating pressure bar/MPa	120/12
Max. pressure (bar/MPa)	150/15
Max. water feed temperature (°C)	up to 60
Power rating (kW)	2.3
Weight (kg)	22
Dimensions (L x W x H) (mm)	360x375x925

Details

Description

The HD 5/12 C Plus is a compact, lightweight, and powerful pressure cleaner for professional use. Featuring a tough, high performance motor and three-piston axial pump, the 5/12 is built to perform. Standard accessories include a Dirt blaster nozzle, enhancing cleaning power for heavy-duty applications, and an Easy Press trigger gun, reducing operator fatigue over longer operating periods.

Accessories

Adapter

Adapter M22 - Swivel

M22 x 1,5female and swivel connection. For extension of high-pressure hoses with AVS connection or for usage of the telescopic lance with a high-pressure hose with AVS connection.

Order no. 4.424-004.0



Automatic, self-winding hose reels

ABS hose reel stainless steel

High-grade, automatic steel hose reel. Especially suitable for use in the food industry. The material and finish provide for a corrosion-resistant, watertight capsuled spring drive. Connection for HP hoses with nipple.

Order no. 2.641-866.0



ABS wall fastening stainless steel

Swivelling wall bracket made of high-grade steel (for 2.641-866). This makes maximum flexibility and convenience possible when working with the HP hose.

Order no. 2.641-867.0



Order no. 6.392-965.0



Order no. 6.392-975.0



Cup foam lance

Cup foam lance

Short, handy foam lance with adjustable spray angle with 1 litre detergent tank. Ideal for cleaning cars due to its compact design.

Order no. 6.394-668.0



Cup foam lance

Tank 1L

Order no. 6.414-954.0



Double lance

Double lance 960 mm

960 mm double lance for variable pressure adjustment on handle at full water flow rate. Suitable for agricultural use (e.g. stable cleaning).

Order no. 6.394-665.0



Flexible spray lance

Flexible lance 1050 mm

1050 mm flexible lance with variable bend from 20° to 140°, ideal for cleaning difficult to reach areas, e.g. gutters.

Order no. 6.394-654.0



Floor and hard surface cleaner

FR Xpert hard surface cleaner

A rotating nozzle beam with Kärcher Power nozzles has an area coverage up to 10 times larger than conventional methods. Plastic cover for good manoeuvrability. Nozzle kit included in delivery. Max. 180 bar / 600 l/h / 60 °C

Order no. 2.641-686.0



Food industry version

High-pressure hose 15 m ID 6, AVS trigger gun connector 11 mm, suitable for food industry, grey

15 m high-pressure hose (DN 6) with patented (rotating) AVS trigger gun connector. Non-discolouring outer layer for use in the food industry. DN 6/155°C/250 bar.

Order no. 6.391-654.0



Gutter cleaner

Gutter cleaning lance

The lance is suited for cleaning of gutter systems. Because of the shape of the lance and the special nozzle the gutter can be cleaned without removing the cover plates.

Order no. 2.642-305.0



Longlife 400

High pressure hose DN 6, 10 m, Longlife


With patented AVS connection in the trigger gun (pivot-mounted).

Order no. 6.391-882.0



High-pressure hose packaged

Order no. 6.391-351.0



Longlife 400 with unions on both sides

High-pressure hose 1.5 m, DN 8, including connectors

1.5 m high-pressure hose (DN 8, M 22 x 1.5) with kink protection and connectors at both ends. For connecting to hose reels with appropriate connector (M 22 x 1.5).


Order no. 6.390-178.0



High pressure hose DN 6, 10 m, drehbar, l


With rotary coupling, 2 x M 22 x 1,5

Order no. 6.391-883.0



High-pressure hose packaged


Order no. 6.391-354.0



High-pressure hose Longlife 400, 15 m, DN 8, including rotary coupling

With rotary coupling, 2 x M 22 x 1.5

Order no. 6.389-709.0



High-pressure hose Longlife 400, 30 m DN 8, including rotary coupling

With rotary coupling, 2 x M 22 x 1.5

Order no. 6.390-294.0



Longlife food industry version

High-pressure hose Longlife 400, 15 m, ID 6, AVS trigger gun connection

Longlife HP hose for use in the food industry. Außendecke## animal-grease-resistant, non-colour-bleeding material. With patented AVS connection in the pistol (pivot mounted)

Order no. 6.391-888.0



Longlife food industry version with unions on both sides

High pressure hose food DN 8 / 10 m

Longlife HP hose for use in the food industry. Außendecke## animal-grease-resistant, non-colour-bleeding material. With rotary coupling, 2 x M 22 x 1,5

Order no. 6.391-864.0



High-pressure hose food industry 400 bar, 20 m, DN 8, including rotary coupling

Longlife HP hose for use in the food industry. Außendecke## animal-grease-resistant, non-colour-bleeding material. With rotary coupling, 2 x M 22 x 1,5

Order no. 6.391-887.0



Nozzle union

Nozzle connector


For protecting and connecting Kärcher power nozzles to spray lances (M 18 x 1.5 IG).

Order no. 5.401-210.0




Pipe cleaning nozzle


Order no. 6.415-944.0



Order no. 6.415-946.0




Order no. 6.415-948.0



Power nozzle spray angle 25°

PCH / Power Nozzle 25250

Order no. 5.765-078.0



Push-on washing brush

Push-on wash brush, M 18 x 1.5

Push-on wash brush for universal use. Simply push on to lance. Connector: M 18 x 1.6.

Order no. 4.762-016.0



Push-on washing brush

Push-on washing brush

With clamp for mounting directly to units' double or triple nozzle. Fits on new double and triple nozzles.

Order no. 4.762-497.0



Quick connect

Quick coupling

For quick change of different spray lances and accessories. Optimum adaption to Kärcher accessories, especially for connection between trigger gun and spray lance. With M22 x 1,5 female.

Order no. 6.401-458.0



Plug nipple

Hardened stainless steel nipple for quick coupling 6.401-458. With M22 x 1,5 male.

Order no. 6.401-459.0



Rotary coupling

Rotary coupling

Kärcher rotary coupling prevents twisting and kinking of high-pressure hoses for ease of use. Connector M 22 x 1.5 m. With grip protection.

Order no. 4.401-091.0



Spacer (including nozzle union)

Spacer (incl. nozzle union)

Guarantees constant safety clearance, e.g. for tyres and bodywork. Helps prevent damage to sensitive surfaces. Mounts directly to lance.

Order no. 5.394-294.0



Spray lance

550 mm lance, non-rotatable

550 mm stainless steel lance. With manual coupling. Non-rotatable.

Order no. 4.760-665.0



Lance 250 mm, non-rotatable

250 mm stainless steel lance. With manual coupling. Non-rotatable.

Order no. 4.760-667.0




standard

High-pressure hose, 10 m, DN 6, 300 bar, AVS trigger gun connection

With patented AVS connection in the trigger gun (pivot-mounted) and hand screw union. M 22 x 1.5 with anti-kink protection. NW 6/155°C/300 bar

Order no. 6.391-875.0



Standard with unions on both sides

High-pressure hose packaged

Order no. 6.391-342.0



High-pressure hose, 30 m DN 8, including rotary coupling

With rotary coupling, 2 x M 22 x 1.5

Order no. 6.390-293.0



Suction filter

Water filter

Order no. 6.414-956.0



Telescopic spray lance

Telescopic jet pipe

Order no. 6.394-690.0



Order no. 6.373-987.0



Trigger guns

High end high-pressure trigger gun

Order no. 4.775-823.0

