



## Mounting Head

**T&B Catalog Number:** TY533MX  
**UPC Number:** 78621087960  
**Status:** Active

### Description:

Cable Tie 18lb 4" Ultraviolet Resistant Black Nylon with Stainless Steel Locking Device #4 Mounting Hole

## Features

- Oval low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time. Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise **bundle** diameter needed.
- The Turned-up Tail orients the tie for easy assembly, making the ties easier to pick up on a flat surface. The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.
- Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the **bundle** and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

## General

Material	Nylon 6.6 Weather Resistant
Color	Black
Mounting Hole Size	#4

## Dimension Information

Nominal Length (inches)	4
Length (inches)	4
Width (inches)	.091
Max. Wire <b>Bundle</b> Diameter (inches)	.625

## Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

## Packaging

Order Multiple	100
Inner Package	100
Outer Package	500
Package Type	Regular
Package Height	3.4
Package Length	5.3
Package Width	4.3
T&B Sold in UOM	Each
T&B Weight Per UOM	0.11 lbs. per 100