



RBK HSS JOBBER DRILL 12.0MM

DIN 338/BS 328

Flute Geometry Standard Helix, right hand spiral

Surface finish Blue

Point geometry Up to 2.9mm - 118° 3.0mm and above - 135° split point

Angle, drill point	118 °
Associated Products	023659
Diameter, External	12.00 mm
Length, effective	101 mm
Length, overall	151 mm
Material	HSS
RoHS Compliant	NA