



Medium grade

Diameter, disc	13 mm
Diameter, external	13 mm
Diameter, shank	3.18 mm
Grade	Medium
RoHS Compliant	NA
Shape	B131
Size	1/2 x 1/2
Size	1/2 x 1/2 "
Size	13 x 13 mm
Speed, rotational max	34500