

## How to Order — Plug

Contact Style	Nomenclature	Part Number	Size	Type	No. of Contacts	Contact Style	Page Reference
<b>Crimp AWG #42-#18</b> (50μ inches Gold, BUMP in Plug)  Note: Crimp Contacts Sold Separately	DL1-156P	110535-0000	DL1	Plastic Body	156 Pin Connector	Crimp	14
	DLM1-156P	127050-0204	DLM1	Metal Body	156 Pin Connector	Crimp	16
	DLD1-156P	111496-0000	DLD1	Plastic Body	156 Pin Connector	Crimp	19
	DL2-96P	110777-0000	DL2	Plastic Body	96 Pin Connector	Crimp	21
	DLM2-96P	127050-0212	DLM2	Metal Body	96 Pin Connector	Crimp	23
	DLD2-96P	111922-0000	DLD2	Plastic Body	96 Pin Connector	Crimp	26
	DL3-60P	110900-0008	DL3	Plastic Body	60 Pin Connector	Crimp	28
	DLM3-60P	127050-0220	DLM3	Metal Body	60 Pin Connector	Crimp	30
	DL4-624P	110959-0002	DL4	Metal Frame	624 Pin Connector	Crimp	33
	DL4-1248P	110959-0003	DL4	Metal Frame	1248 Pin Connector	Crimp	**
	DL4-2496P	110959-0004	DL4	Metal Frame	2496 Pin Connector	Crimp	**
	DL5-260P	111986-0014	DL5	Plastic Body	260 Pin Connector	Crimp	35
DLM5-260P	127050-0109	DLM5	Metal Body	260 Pin Connector	Crimp	37	
DLM6-360P	127050-0034	DLM6	Metal Body	360 Pin Connector	Crimp	40	
<b>Square Post 7,11 (.280) Ext.</b> 50μ inches Gold, BUMP Std. Square Post □ 0,64 (.025) Factory Installed Solder to PCB Through Hole Interconnect Termination	DL1-156PW6A*	110535-0030	DL1	Plastic Body	156 Pin Connector	Square Post	15
	DLM1-156PW6A*	112134-0000	DLM1	Metal Body	156 Pin Connector	Square Post	17
	DLD1-156PW6A*	111496-0002	DLD1	Plastic Body	156 Pin Connector	Square Post	20
	DL2-96PW6A*	110777-0025	DL2	Plastic Body	96 Pin Connector	Square Post	22
	DLM2-96PW6A*	112136-0000	DLM2	Metal Body	96 Pin Connector	Square Post	24
	DLD2-96PW6A*	111922-0002	DLD2	Plastic Body	96 Pin Connector	Square Post	27
	DL3-60PW6A*	110900-0014	DL3	Plastic Body	60 Pin Connector	Square Post	29
	DLM3-60PW6A*	112138-0000	DLM3	Metal Body	60 Pin Connector	Square Post	31
	DL4-624PW6A*	110959-0042	DL4	Metal Frame	624 Pin Connector	Square Post	34
	DL5-260PW6A*	111986-0000	DL5	Plastic Body	260 Pin Connector	Square Post	36
	DLM5-260PW6A*	112086-0000	DLM5	Metal Body	260 Pin Connector	Square Post	38
	DLM6-360PW6A*	111995-0000	DLM6	Metal Body	360 Pin Connector	Square Post	41
<b>Square Post 3,18 (.125) Ext.</b> 50μ inches Gold, BUMP Std. Square Post □ 0,64 (.025) Factory Installed Solder to PCB Through Hole	DL110535-40	110535-0040	DL1	Plastic Body	156 Pin Connector	Square Post	15
	DLM112134-2	112134-0002	DLM1	Metal Body	156 Pin Connector	Square Post	17
	DLM112136-2	112136-0002	DLM2	Metal Body	96 Pin Connector	Square Post	24
	DLM112138-2	112138-0002	DLM3	Metal Body	60 Pin Connector	Square Post	31
	DLM112086-3	112086-0003	DLM5	Metal Body	260 Pin Connector	Square Post	38
	DLM111995-7	111995-0007	DLM6	Metal Body	360 Pin Connector	Square Post	41
	<b>Wrap Post 15,37 (.605) Ext.</b> 50μ inches Gold, BUMP Std. Square Post □ 0,64 (.025) Factory Installed	DL1-156PW4A*	110535-0025	DL1	Plastic Body	156 Pin Connector	Wrap Post
DLM1-156PW4A*		112134-0001	DLM1	Metal Body	156 Pin Connector	Wrap Post	17
DLD1-156PW4A*		111496-0001	DLD1	Plastic Body	156 Pin Connector	Wrap Post	20
DL2-96PW4A*		110777-0022	DL2	Plastic Body	96 Pin Connector	Wrap Post	22
DLM2-96PW4A*		112136-0001	DLM2	Metal Body	96 Pin Connector	Wrap Post	24
DLD2-96PW4A*		111922-0001	DLD2	Plastic Body	96 Pin Connector	Wrap Post	27
DL3-60PW4A*		110900-0013	DL3	Plastic Body	60 Pin Connector	Wrap Post	29
DLM3-60PW4A*		112138-0001	DLM3	Metal Body	60 Pin Connector	Wrap Post	31
DL4-624PW4A*		110959-0035	DL4	Metal Frame	624 Pin Connector	Wrap Post	34
DL5-260PW4A*		111986-0003	DL5	Plastic Body	260 Pin Connector	Wrap Post	36
DLM5-260PW4A*		112086-0002	DLM5	Metal Body	260 Pin Connector	Wrap Post	38
DLM6-360PW4A*		111995-0001	DLM6	Metal Body	360 Pin Connector	Wrap Post	41
<b>Square Post 7,11 (.280) Ext.</b> 20μ inches Gold, Hermaphroditic Std. Square Post □ 0,64 (.025) Factory Installed Solder to PCB Through Hole	DL1-156PW6	110535-0026	DL1	Plastic Body	156 Pin Connector	Square Post	15
<b>Wrap Post 15,37 (.605) Ext.</b> 20μ inches Gold, Hermaphroditic Std. Square Post □ 0,64 (.025) Factory Installed	DL1-156PW4	110535-0012	DL1	Plastic Body	156 Pin Connector	Wrap Post	15
	DL2-96PW4	110777-0008	DL2	Plastic Body	96 Pin Connector	Wrap Post	22
	DL3-60PW4	110900-0006	DL3	Plastic Body	60 Pin Connector	Wrap Post	29
	DL4-624PW4	110959-0011	DL4	Metal Frame	624 Pin Connector	Wrap Post	34
<b>PC / RC 4,50 (.177) Ext.</b> 20μ inches Gold - 4 A max. Round Tail - ∅ 0,50 (.020) Factory Installed Solder to PCB Through Hole	DLM1-156PC	127050-0207	DLM1	Metal Body	156 Pin Connector	PC	18
	DLM2-96PC	127050-0215	DLM2	Metal Body	96 Pin Connector	PC	25
	DLM3-60PC	127050-0223	DLM3	Metal Body	60 Pin Connector	PC	32
	DLM5-260PC	127050-0111	DLM5	Metal Body	260 Pin Connector	PC	39
	DLM6-360PC	127050-0097	DLM6	Metal Body	360 Pin Connector	PC	42

Note: 50μ inches gold contacts (Bump on plug side, Flat on receptacle side) are mandatory for applications with less than 100 milliamps.