

- Replacement for 35 W MR16 halogen lamp
- Binned in a 4-step level to provide good colour consistency
- Warm white
- Dimmable
- Lifetime of 25,000 hrs
- Suitable replacement for halogen or incandescent spots. Perfect for accent and general lighting.



Order Code 52206

General Data

Lamp Socket	GU5.3
Design	Lens

Geometric Data

Length (mm)	58
Diameter (mm)	50
Weight (g)	50

Electric Data

Wattage (W)	7
Voltage (V)	12 V AC/DC
Power Factor	0,75
Operating Frequency (Hz)	50-60

Photometric Data

Luminous Flux (lm)	390
CRI	≥ 80
CCT (K)	2700
Luminous Intensity (cd)	850
Beam Angle (°)	35
Lifetime (hrs)	25,000

Switching cycle 18,000

Wattage Equivalent (W) 35





Order Code 52206

Product Description LED MR16 GU5.3 7W 2700K WW 390LM 35deg DIM

Technical Packaging Details

Barcode	023942522065
EAN 128	(02)00023942522065(37)40(91)162
EAN 14	50023942522060
Pack Dimensions (HxWxL) mm	62 x 50 x 50
Pack Weight	77 g
MOQ	10
Carton Dimensions (HxWxL) mm	330 x 300 x 150
Cartons/Pallet	51
Layers/Pallet	6
Units/Pallet	2040

Photometric Diagram

52206

