

Produkt Informationen



WX 2021 Set

Bestellnummer : T0053422699



Power unit with 2 channels

Power unit WX 2, 200 W, soldering iron WXMP, 55 W, 12 V, with Active Tip Technology, soldering tip RT 3, safety rest WDH 51, micro tweezers WXMT, 2 x 40 W, 12 V, with Active Tip Technology, standard tip RTW 2 and safety rest WDH 60 with dry cleaner

Technical Data

This station is ESD safe.



Dimensions L x W x H:	170 x 151 x 130 mm (6,69 x 5,94 x 5,12 inch)
Weight:	approx. 3,2 kg
Channels:	2
Power supply:	230 V, 50 Hz
Power consumption:	200 W (255 W)
Protection class:	I
Temperature range:	Adjustable from 50°C - 550°C (150°F - 999°C) Adjustable temperature range varies among tools
Temperature accuracy:	± 9°C (± 17°F)
Temperature stability:	± 2°C (± 4°F)
Equipotential bonding:	Via 3,5 mm pawl socket on back of device
Material touch panel:	Made of antistatic coated material
Dimensions touch panel:	74 x 38 mm
Resolution:	255 x 127 (128) dots
Display backlighting:	4 LEDs

Equipotential bonding:

The 3,5 mm switch offers four different options:

- a) Hard grounded without plug (original delivery)
- b) Equipotential bonding: with plug, compensation line on center contact
- c) Potential free: with plug
- d) Soft grounded: with plug and soldered resistor grounded via selected resistor

USB interface:

USB interface in front of firmware updates, parameterization and monitoring
 USB interface supports all standard USB flash drive types

Power unit WX 2

- Innovative operation concept
- Robust touch screen with ESD safe glass
- Intuitive use with turn-click-wheel with enter key and finger guide.
- Blue LED backlighting
- Multilingual menu navigation
- High functionality
- No safety rest with Stop & Go function needed thanks to integrated acceleration sensor
- Optimized precision, better stability by sensor in the soldering iron
- Specific parameterization of tool by storage medium in hand piece.
- Visual process control via blue LED ring light
- All WX tools connectable