

RMCS9018BK1	RMCV9018BK1	1.73	8.50	8.00	1U	1.75	0.81	-
RMCS19018BK1	RMCV19018BK1	1.73	17.00	8.00	1U	1.75	0.81	-
RMCS190113BK1	RMCV190113BK1	1.73	17.00	13.00	1U	1.75	0.81	-
RMCS9038BK1	RMCV9038BK1	3.48	8.50	8.00	2U	3.50	2.56	1427P
RMCS19038BK1	RMCV19038BK1	3.48	17.00	8.00	2U	3.50	2.56	1427P
RMCS190313BK1	RMCV190313BK1	3.48	17.00	13.00	2U	3.50	2.56	1427P
RMCS9058BK1	RMCV9058BK1	5.23	8.50	8.00	3U	5.25	4.31	1427N
RMCS190513BK1	RMCV190513BK1	5.23	17.00	13.00	3U	5.25	4.31	1427N
RMCS190713BK1	RMCV190713BK1	6.98	17.00	13.00	4U	7.00	6.06	1427M
RMCS190813BK1	RMCV190813BK1	8.73	17.00	13.00	5U	8.75	7.81	1427M
RMCS191013BK1	RMCV191013BK1	10.48	17.00	13.00	6U	10.50	9.56	1427L
RMCS191015BK1	RMCV191015BK1	10.48	17.00	15.00	6U	10.50	9.56	1427L

Front & Rear Replacement Panels (Full 17" Width Only)

Part No.	Part No.	Part No.	Mounting Dimensions	
			Height	Rack Units
Textured Black	Smooth Black	Beige		
RMCP1	RMCP1BK	RMCP1CG	1.75	1U
RMCP1	RMCP1BK	RMCP1CG	1.75	1U
RMCP3	RMCP3BK	RMCP3CG	3.5	2U
RMCP3	RMCP3BK	RMCP3CG	3.5	2U
RMCP5	RMCP5BK	RMCP5CG	5.25	3U
RMCP7	RMCP7BK	RMCP7CG	7	4U
RMCP8	RMCP8BK	RMCP8CG	8.75	5U
RMCP10	RMCP10BK	RMCP10CG	10.5	6U
RMCP10	RMCP10BK	RMCP10CG	10.5	6U

Internal Aluminum Chassis Panel

Part No.	Overall Panel Dimensions			For use with Enclosure Dimensions	
	Height	Width	Depth	Width	Depth
RMP908	0.50	8.22	6.00	8.50	8.00
RMP1908	0.50	16.72	6.00	17.00	8.00
RMP1913	0.50	16.72	11.00	17.00	13.00
RMP1915	0.50	16.72	13.00	17.00	15.00

Data subject to change without notice.