

DVI-D Cables
Various Lengths



- DVI-D dual link plug to plug leads
- OFC Cable with ferrite suppressors
- Molded plastic plugs with thumb screws
- Gold plated connectors
- 1, 1.8, 3, 5, 7 and 10m lengths available

NEW

656080

Mfrs. List No.	Cable Length	Order Code	Price Each		
			1+	10+	25+
PSG03323	1m	209-9523 ●	6.03	5.55	5.02
PSG03324	1.8m	209-9525 ●	7.46	6.87	6.21
PSG03325	3m	209-9526 ●	9.89	9.11	8.24
PSG03326	5m	209-9527 ●	13.63	12.55	11.36
PSG03327	7m	209-9528 ●	18.77	17.29	15.64
PSG03328	10m	209-9529 ●	25.29	23.29	21.07