



Sample photo

Order symbol: UL PC 233011
Product nbr: 7042890
Description: UL Enclosure, PC
Remarks: Grey cover

EAN: 6418074054418
El. number:
Finland:
Denmark: 8212032156
Italy: 7301065U
Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:			Length	Width	Height	Rating:
mm:			230	300	110	Ingress Protection (EN 60529): IP 66/67
inch:			9.1	11.8	4.3	Impact Resistance (EN 62262): IK 08/07
Materials:						Electrical insulation: Totally insulated
Material:			Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:			RAL 7035			UV resistance: UL 508
Cover colour:			RAL 7035			Flammability Rating (UL 746 C 5): UL 746C 5V
Cover screws material:			Stainless steel			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:			Polyurethane			UL Type: UL TYPE 1, 4, 4X, 12, 13
Temperatures:						Certificates:
Short term:			-40 ... 120 °C			Underwriters Laboratories
Continuous:			-40 ... 80 °C			Fimko
Short term:			-40 ... 250 °F			Europe EN 62208: 2003
Continuous:			-40 ... 175 °F			UL Canada
Accessories:						Gost R

EURONORD PC/ABS 300x230x87-110

