

Item no.: 224-201
Product description: SERVICE CONNECTOR



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Product group	7 (Push Wire Conn.)
Cross section [mm ²]	0.5 - 2.5 mm ²
Cross section [AWG]	20 - 16 AWG
Wiring method	e+f
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	400 V
Measured shock voltage	4 kV
Pollution degree	2
Current intensity EN	24 A
Weight	4.4 g
Color	gray
Wiring type	Side-entry
No. of connection Points	2
No. of potentials	1
Height	15.5 mm
Height	0.61 in
Width	8.5 mm
Width	0.335 in
Depth	42 mm

Depth	1.654 in
Strip length from	9 mm
Strip length to	11 mm
Strip length	0.39 in



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
224-201	ABS	10-HN17750340X	400	24	0,5-2,5
224-201	BV	11914/BO	300	24	2,5
224-201	CCA	DK2527	400	24	2,5
224-201	CSA	154112-1059435	300		20-16
224-201	DEMKO	143835-01	400	24	2,5
224-201	DNV	E-9215	400	24	0,5-2,5
224-201	FIMKO	163400-01			2,5
224-201	GL	17294-00HH	300	24	2,5
224-201	KEMA	96.1739.01	400	24	2,5
224-201	LR	04/20013(E3)	400	24	2,5
224-201	NEMKO	P96191377			2,5
224-201	ÖVE	1193-032-02	400	24	0,5-2,5
224-201	PSE	JET0695-43040-1001	300	20	20-16
224-201	RMR	11130002	400	24	0,5-2,5
224-201	RosTest	AB24 B04007			
224-201	SEMKO	9617079			2,5
224-201	UL listed	E69654	300	20	20-16
224-201	VDE	Ausweis.Nr.40022792	400	24	2,5

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected