



Aluminum Chassis & Bottom Plates (1444 & 1434 Series)

- Home
- Products
- Distributors
- Technical
- Contact Us
- Other Options

Path: [Home](#) > [Enclosure Index](#) > **Aluminum Chassis**



click to enlarge

Shipped with plastic skin protection
























click to enlarge






















**Natural Finish
(Shown with protective plastic skin removed)**










Key Features:

- Spot welded heavy duty construction chassis.
- Natural finish as shown above - protected through manufacturing and shipping with a plastic skin cover to ensure a high quality finish.
- Optional bottom plates are punched with 4 holes – 3/16” diameter (Chassis requires drilling to install optional bottom plates).
- Hardware not provided, please order separately - Part number **1421J6** (Pkg. of 6, 6-32 Philips head screws).
- Link here to [rubber feet options](#).
- Link here to [perforated chassis covers](#).
- UPGRADE to our [Aluminum Chassis with Walnut Sides](#) .

Part Number		PDF Reader File	AutoCAD .dwg File (zipped)	3D Solid Model .igs & .stp files (zipped)	Thick (Inches)	Units	Dimensions		
Aluminum Chassis	Bottom Plate						Width	Depth	Height
1444-6	1434-6	127K	153K	108K	0.04	inch	4	4	2
						mm	102	102	51
1444-45351	1434-4535	NEW	NEW	NEW	0.04	inch	4.5	3.5	1
						mm	114	89	25
1444-542	1434-54	NEW	NEW	NEW	0.04	inch	5	4	2
						mm	127	102	51




1444-6415	1434-8	NEW	NEW	NEW	0.04	inch	6	4	1.5
						mm	152	102	38
1444-8	1434-8				0.04	inch	6	4	2
						mm	152	102	51
		228K	152K	108K					
1444-643	1434-8	NEW	NEW	NEW	0.04	inch	6	4	3
						mm	152	102	76
1444-12	1434-12				0.04	inch	7	5	2
						mm	178	127	51
		224K	159K	108K					
1444-753	1434-12	NEW	NEW	NEW	0.04	inch	7	5	3
						mm	178	127	76
1444-772	1434-77	NEW	NEW	NEW	0.04	inch	7	7	2
						mm	178	178	51
1444-9	1434-10				0.04	inch	8	4	1
						mm	203	102	25
		211K	148K	90K					
1444-10	1434-10				0.04	inch	8	4	2
						mm	203	102	51
		212K	162K	108K					
1444-84515	1434-845	NEW	NEW	NEW	0.04	inch	8	4.5	1.5
						mm	203	114	38
1444-862	1434-86	NEW	NEW	NEW	0.04	inch	8	6	2
						mm	203	152	51
1444-14	1434-14				0.04	inch	9	5	2
						mm	229	127	51
		210K	157K	109K					
1444-972	1434-97	NEW	NEW	NEW	0.04	inch	9	7	2
						mm	229	178	51
1444-9552	1434-955	NEW	NEW	NEW	0.04	inch	9.5	5	2
						mm	241	127	51
1444-95525	1434-955	NEW	NEW	NEW	0.04	inch	9.5	5	2.5
						mm	241	127	64
1444-9553	1434-955	NEW	NEW	NEW	0.04	inch	9.5	5	3
						mm	241	127	76
1444-1053	1434-105	NEW	NEW	NEW	0.04	inch	10	5	3
						mm	254	127	76
1444-15	1434-16				0.04	inch	10	6	1
						mm	254	152	25
		207K	148K	91K					
1444-16	1434-16				0.04	inch	10	6	2
						mm	254	152	51
		202K	150K	88K					
1444-10825	1434-108	NEW	NEW	NEW	0.04	inch	10	8	2.5
						mm	254	203	64

1444-1172	1434-117	NEW	NEW	NEW	0.04	inch	11	7	2
						mm	279	178	51
1444-1273	1434-127	NEW	NEW	NEW	0.04	inch	12	7	3
						mm	305	178	76
1444-22	1434-22				0.051	inch	12	8	2
						mm	305	203	51
1444-12825	1434-22	NEW	NEW	NEW	0.051	inch	12	8	2.5
						mm	305	203	64
1444-24	1434-22				0.051	inch	12	8	3
						mm	305	203	76
1444-29	1434-29				0.051	inch	12	10	2
						mm	305	254	51
1444-12103	1434-29	NEW	NEW	NEW	0.051	inch	12	10	3
						mm	305	254	76
1444-12123	1434-1212	NEW	NEW	NEW	0.051	inch	12	12	3
						mm	305	305	76
1444-1372	1434-137	NEW	NEW	NEW	0.04	inch	13	7	2
						mm	330	178	51
1444-18	1434-18				0.04	inch	13.5	5	2
						mm	343	127	51
1444-1463	1434-146	NEW	NEW	NEW	0.051	inch	14	6	3
						mm	356	152	76
1444-14103	1434-1410	NEW	NEW	NEW	0.051	inch	14	10	3
						mm	356	254	76
1444-1573	1434-157	NEW	NEW	NEW	0.051	inch	15	7	3
						mm	381	178	76
1444-1593	1434-159	NEW	NEW	NEW	0.051	inch	15	9	3
						mm	381	229	76
1444-26	1434-26				0.051	inch	16	8	2
						mm	406	203	51
1444-28	1434-26				0.051	inch	16	8	3
						mm	406	203	76
1444-20	1434-20				0.04	inch	17	4	3
						mm	432	102	76
1444-1763	1434-176	NEW	NEW	NEW	0.051	inch	17	6	3
						mm	432	152	76
1444-1773	1434-177	NEW	NEW	NEW	0.051	inch	17	7	3
						mm	432	178	76

1444-1783	1434-178	NEW	NEW	NEW	0.051	inch	17	8	3
						mm	432	203	76
1444-30	1434-30	 185K	 164K	 116K	0.051	inch	17	10	2
						mm	432	254	51
1444-32	1434-30	 174K	 160K	 116K	0.051	inch	17	10	3
						mm	432	254	76
1444-33	1434-30	 172K	 160K	 116K	0.051	inch	17	10	4
						mm	432	254	102
1444-17105	1434-30	NEW	NEW	NEW	0.051	inch	17	10	5
						mm	432	254	127
1444-17123	1434-1712	NEW	NEW	NEW	0.051	inch	17	12	3
						mm	432	305	76
1444-17132	1434-1713	NEW	NEW	NEW	0.051	inch	17	13	2
						mm	432	330	51
1444-17133	1434-1713	NEW	NEW	NEW	0.051	inch	17	13	3
						mm	432	330	76
1444-17134	1434-1713	NEW	NEW	NEW	0.051	inch	17	13	4
						mm	432	330	102
1444-17135	1434-1713	NEW	NEW	NEW	0.051	inch	17	13	5
						mm	432	330	127
1444-17143	1434-1714	NEW	NEW	NEW	0.051	inch	17	14	3
						mm	432	356	76
1444-17154	1434-1715	NEW	NEW	NEW	0.051	inch	17	15	4
						mm	432	381	102
1444-17156	1434-1715	NEW	NEW	NEW	0.051	inch	17	15	6
						mm	432	381	152
1444-17173	1434-1717	NEW	NEW	NEW	0.051	inch	17	17	3
						mm	432	432	76
1444-17174	1434-1717	NEW	NEW	NEW	0.051	inch	17	17	4
						mm	432	432	102

Views:

Upside Down (to show interior)	Optional Bottom Plate

 <p>click to enlarge</p>	 <p>click to enlarge</p>
UPGRADE to our Aluminum Chassis with Walnut Sides	
 <p>link here</p>	



catalog pages on this series (98K) [9C-1444.pdf](#)

Exactly what you are looking for???

Link to our stocking distributors - most have "on-line" pricing, stock check and ordering!!!

Our Distributors

[Order from your favorite distributor](#)

[Home](#) | [Products](#) | [Distributors](#) | [Technical](#) | [Contact Us](#) | [Other Options](#)

Copyright; © 1997-2012 Hammond Mfg Co Inc
URL: <http://www.hammondmfg.com>