

Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

## Model #: LC1200

## Line Conditioner / AVR System - Automatic voltage regulator / Power conditioner / AC surge suppressor



## **Highlights**

- Premium automatic voltage regulation (AVR), power conditioning and AC surge suppression
- Maintains regulated 120V nominal output over an input range of 89 to 147V
- 1200 watt / 10 amp capacity
- 4 NEMA 5-15R outlets, 7 foot AC cord
- LEDs display incoming voltage range, surge suppression and line fault status
- \$25,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

## **Description**

1200 watt Automatic Voltage Regulation (AVR) system. Protects sensitive electronics, computer accessories and home theater equipment from power-related damage and performance problems. Extends the useful life of connected equipment by providing optimum voltage conditions for enhanced efficiency and cooler internal operating temperatures. Reliable transformer-based voltage correction circuits maintain 120V nominal output during voltage fluctuations between 89 and 147V. Three levels of voltage stabilization offer targeted response for overvoltages, undervoltages and severe brownouts. Prevents equipment damage and power related performance problems for computer accessories, printers, home theater equipment, a/v components and other sensitive electronic devices. Network-grade AC surge and EMI/RFI noise suppression. Supports loads up to 1200 watts, 10A. Includes 4 AC outlets, 7 ft AC line cord and 7 diagnostic LEDs which display incoming voltage level, surge suppression status and line fault status. \$25,00connected equipment insurance (USA and Canada Only).

#### **Applications**

• Maintains regulated output voltage during severe brownouts and overvoltages for computer accessories, printers, home theater equipment, a/v components, point-of-sale equipment, and other applications requiring clean, regulated AC power.

#### Package Includes

- LC1200 Line Conditioner
- Instruction manual

#### **Features**

- Maintains usable 120V (+10%/-12%) nominal output over an input range of 89 to 147V
- Protects sensitive electronics, computer accessories and home theater equipment from power-related damage and performance problems
- Extends the useful life of connected equipment by providing optimum voltage conditions for enhanced efficiency and cooler internal operating temperatures
- Three levels of voltage stabilization offer targeted response to overvoltages, undervoltages and severe brownouts
- Input voltages over 128V are reduced by 9.6% (+/- 3V)
- Input voltages between 103 and 112V are boosted by 8.9% (+/- 3V)
- Input voltages below 102V are boosted by 18.8% (+/- 3V)
- 1200 watts output power rating supports 120V loads up to 10 amps
- Network grade AC surge suppression
- Premium EMI/RFI noise filtering prevents equipment interaction, system interference, lockups and other power-related audio and video

artifacts

- $\bullet$  7 diagnostic LEDs indicate input voltage levels, surge suppression status and line fault conditions
- 4 protected NEMA5-15R outlets
- 7 foot AC power cord with NEMA5-15P input plug
- \$25,000 Ultimate Lifetime Insurance for connected equipment (USA and Canada Only)

# **Specifications**

OUTPUT	
Output VA	1200
Output watts	1200
Output nominal voltage	120V / 60Hz
Outlet quantity / type	4 NEMA 5-15R
INPUT	
Input cord length (ft.)	7
Input cord length (m)	1.83
LEDS ALARMS & SWITCHES	
Front panel LEDs	7 LEDs show incoming voltage status, protection present and line fault conditions
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	1200 joules, conforms to IEEE 587 / ANSI C62.41 specifications
EMI / RFI AC noise suppression	75 dB
UPC Codes	
Unit Carton UPC#	037332040022
PHYSICAL	
Shipping weight (lbs)	8.7
Shipping weight (kg)	4
Unit Dimensions (HWD/in)	7.25 x 6 x 7
Unit Dimensions (HWD/cm)	18.4 x 15.2 x 17.8
Material of construction	Plastic
Form factors supported	Small Tower
CERTIFICATIONS	
Certifications	Tested to UL1012 (USA), cUL1012 (Canada), NOM (Mexico)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 Ultimate Lifetime Insurance

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?variables.txtModelID=208.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.