

Tripp Lite 1111 West 35th Street Chicago, IL 60609 USA Telephone: +(773) 869 1234

E-mail: saleshelp@tripplite.com

Model #: 4SPDX

Waber-by-Tripp Lite 4-outlet Power Strip with 6-ft. Cord



Highlights

- 4 outlets
- 7.38 in. length
- · Lighted master switch
- All-metal housing

Description

The Waber-by-Tripp Lite 4SPDX Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 4 NEMA 5-15R output receptacles with 1.520-in. center-to-center spacing, 6-foot AC line cord and keyhole mounting for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes the 4SPDX ideal for distributing alternate waveform UPS or generator power. Features rugged metal housing, lighted power switch with integrated 15A resettable circuit breaker and attractive beige color scheme.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 4 NEMA 5-15R

ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT - Corded power distribution strip

Applications

• Offers multiple outlet power distribution in workbench, wallmount or floor mount applications. Unfiltered electrical pass-through makes the 4SPDX ideal for distributing alternate waveform UPS or generator power to protected equipment.

Package Includes

- 4SPDX Power Strip
- Warranty information
- Instruction manual

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 4 NEMA 5-15R output receptacles with 1.520-in. center-to-center spacing
- Lighted combination power switch with integrated circuit breaker
- Keyhole mounting support permanent installation on a wide variety of surfaces
- UL1363 (USA), cUL (Canada)
- 15A power handling capacity
- 6-ft. AC line cord

Specifications

ОИТРИТ	
Frequency compatibility	50 / 60 Hz
Circuit Breaker (amps)	15
Outlet quantity / type	4 NEMA 5-15R
Outlet spacing	1.520 in.
Outlet orientation	Single row of 4
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input connection type	NEMA 5-15P
Input cord length (ft.)	6
Input cord length (m)	1.8288
Voltage compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	Lighted combination switch / circuit breaker
PHYSICAL	
Unit Dimensions (HWD/in)	7.5 x 2.5 x 1.5
Unit Dimensions (HWD/cm)	19.1 x 6.4 x 3.8
Material of construction	Metal
Integrated keyhole mounting tabs	Keyhole mounting tabs enable mounting to a variety of surfaces
Receptacle Color	Beige
AC line cord color	Beige
Outlets center to center measurement	30mm
Keyhole slot center to center measurement	127mm
CERTIFICATIONS	
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?variables.txtModelID=1962.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.