



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: PS4816

16-outlet Vertical Power Strip with 15-ft. Cord

Highlights

- 16 outlets
- Convenient and safe covered, on/off switch
- 15-amp circuit breaker
- 15-ft. cord
- 48" length



Description

Tripp Lite's PS4816 power strip offers 15 amp, 120V multi-outlet AC power distribution in a convenient 48 inch mountable housing. Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications. Includes 16 NEMA 5-15R output receptacles with 2.717 inch center-to-center spacing, 15 ft AC line cord and lighted power switch with locking transparent cover to prevent accidental shutoff. Sturdy all-metal extruded aluminum housing stands up to demanding network, laboratory or factory environments.

INPUT/OUTPUT: Input: NEMA 5-15P/Output: 16 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: 48 in. corded, mountable power strip

Applications

- Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications

Package Includes

- PS4816
- Mounting hardware
- Instruction manual

Features

- Sturdy all-metal 48 inch corded strip format with 2.717 inch center-to-center outlet spacing
- Includes 16 NEMA 5-15R output receptacles
- Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications
- Lighted power switch with locking transparent cover prevents accidental shutoff
- 15 amp electrical capacity with circuit breaker
- 120VAC, 50/60Hz electrical compatibility

Specifications

OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Circuit Breaker (amps)	15

Outlet quantity / type	16 Nema 5-15R
Outlet spacing	2.717 in.
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input connection type	Nema 5-15P
Input plug features	Black
Input cord length (ft.)	15
Input cord length (m)	4.572
Input cord gauge, type	14/3 SJT
Voltage compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	Lighted 2 position switch controls power to all outlets
Locking switch cover	Transparent on/off switch cover prevents accidental turn-off
PHYSICAL	
Unit Dimensions (HWD/in)	48 x 1.5 x 1.5
Unit Dimensions (HWD/cm)	122 x 3.8 x 3.8
Unit weight (lbs)	4.3
Unit weight (kg)	1.9522
Material of construction	Aluminum
Mounting accessories included	Includes mounting clips
Receptacle Color	Black
AC line cord color	Black
Form factors supported	Supports horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications
Outlets center to center measurement	69mm
CERTIFICATIONS	
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?variables.txtModelID=194.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.