



Features & Benefits

- ✘ Conforms fully to TIA/EIA-568-B
- ✘ Lengths available from 0.5 to 5 metres
- ✘ Available in nine different colours
- ✘ Each lead is individually tested
- ✘ Plugs conform to ISO8877
- ✘ Individually QA tested

Connectix Enhanced Category 5 UTP Patch Leads are designed to exceed the performance requirements of the Enhanced Category 5 specification.

Connectix leads are made from Enhanced Category 5 stranded cable and are terminated using high performance modular plugs.

Connectix Patch Leads are made from Enhanced Category 5 stranded cable and are terminated using high performance modular plugs.

Each lead is individually factory tested to the standard to ensure true standard compatibility.

We stock a variety of booted and unbooted leads in lengths from 0.5 to 5 metres, available in a number of different colours.

Specification

Plug	High Performance Modular Plug
Cable	Enhanced Category 5 Stranded Cable
Conforms to	TIA/EIA-568-B

Ordering Information

Cat 5E UTP Patch Lead

Colour	Length (metre)	Part Number	Length (metre)	Part Number
Grey	0.5	003-3NB4-005-01	1.0	003-3NB4-010-01
White	0.5	003-3NB4-005-02	1.0	003-3NB4-010-02
Blue	0.5	003-3NB4-005-03	1.0	003-3NB4-010-03
Green	0.5	003-3NB4-005-04	1.0	003-3NB4-010-04
Red	0.5	003-3NB4-005-05	1.0	003-3NB4-010-05
Yellow	0.5	003-3NB4-005-06	1.0	003-3NB4-010-06
Orange	0.5	003-3NB4-005-07	1.0	003-3NB4-010-07
Purple	0.5	003-3NB4-005-08	1.0	003-3NB4-010-08
Black	0.5	003-3NB4-005-09	1.0	003-3NB4-010-09
Grey	2.0	003-3NB4-020-01	3.0	003-3NB4-030-01
White	2.0	003-3NB4-020-02	3.0	003-3NB4-030-02
Blue	2.0	003-3NB4-020-03	3.0	003-3NB4-030-03
Green	2.0	003-3NB4-020-04	3.0	003-3NB4-030-04
Red	2.0	003-3NB4-020-05	3.0	003-3NB4-030-05
Yellow	2.0	003-3NB4-020-06	3.0	003-3NB4-030-06
Orange	2.0	003-3NB4-020-07	3.0	003-3NB4-030-07
Purple	2.0	003-3NB4-020-08	3.0	003-3NB4-030-08
Black	2.0	003-3NB4-020-09	3.0	003-3NB4-030-09
Grey	4.0	003-3NB4-040-01	5.0	003-3NB4-050-01
White	4.0	003-3NB4-040-02	5.0	003-3NB4-050-02
Blue	4.0	003-3NB4-040-03	5.0	003-3NB4-050-03
Green	4.0	003-3NB4-040-04	5.0	003-3NB4-050-04
Red	4.0	003-3NB4-040-05	5.0	003-3NB4-050-05
Yellow	4.0	003-3NB4-040-06	5.0	003-3NB4-050-06
Orange	4.0	003-3NB4-040-07	5.0	003-3NB4-050-07
Purple	4.0	003-3NB4-040-08	5.0	003-3NB4-050-08
Black	4.0	003-3NB4-040-09	5.0	003-3NB4-050-09