



NOTES:

1. HANDLE-NICKEL PLATED
2. FITS .328 O.D. PHONO JACK
3. ACCEPTS CABLES UP TO .203 IN. DIA.

CUSTOMER DRAWING

★	STAR SYMBOL DENOTES CRITICAL DIMENSION. SEE S/C ENGINEERING STANDARD ES-0001	SIZE	WIDTH	MULT	LB PER LB	TEMPER
	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT, INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSE ONLY					
	UNLESS OTHERWISE SPECIFIED:	DRAWN BY	DATE	FINISH		
	1 DECIMAL DIMENSIONS ± .008 2 FRACTIONAL DIMENSIONS ± 1/64 3 ANGLES ± 1/2° 4 ALL DIA'S CONCENTRIC WITHIN .005 T.I.R 5 ALL DIMENSIONS IN INCHES 6 FOR THREADS USE UNIFIED PLUG AND RING GAGES ONLY 7 REMOVE ALL BURRS 8 PART TO BE FABRICATED AS SPECIFIED MAKE NO DIMENSIONAL ALLOWANCES FOR APPLIED FINISHES, IE PLATING, PAINTING, ETC 9 HOLES ON SAME CENTERLINE MUST BE ALIGNED WITHIN ± .008	IAC	11-5-90	PER FINISH SPEC. NO. _____		
	CHECKED BY	DATE	MATERIAL			
	IAC	11-5-90	PER MAT. SPEC. NO. _____			
	APPROVED BY	DATE	Switchcraft®			
	J. VONDER	11-5-90				
	SCALE	4:1		FIRST USED ON		
	NAME	PHONO PLUG		PART NO.	ISSUE	
				3502		
				SHEET 1 OF 1		
	DO NOT SCALE DRAWING					

DATE	11-5-90																						
BY	IAC	JL	TNO																				
REVISION	FIRST DRAWN	ECO 16417	ECO 20627																				
ISS	A	B	D																				