

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [08-50-0032](#)
Status: **Active**
Overview: [KK® Interconnection System](#)
Description: [KK® Cat Ear Crimp Terminal 4809, 22-30 AWG, Hot Tin, Bag](#)

Documents:

[3D Model](#) [Product Specification PS-99020-0088 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-10-07 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	4809
Application	Signal
Crimp Quality Equipment	Yes
Overview	KK® Interconnection System
Packaging Alternative	08-50-0031 (Reel)
Product Name	Cat Ear, KK®
UPC	800753746206

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.040/g
Packaging Type	Bag
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.57mm max.
Wire Size AWG	22, 24, 26, 28, 30
Wire Size mm²	N/A

Material Info

Old Part Number 4809C-(P918)L

Reference - Drawing Numbers

Product Specification [PS-10-07](#), [PS-99020-0088](#)
 Sales Drawing [SD-4809-*](#), [SD-4809C-****](#)



EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[4809Series](#)

Use With

[6471](#) 2.54mm Pitch KK® Crimp Terminal Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Insertion Tool	0638120000
Extraction Tool	0011030022
Hand Crimp Tool	0638118200