

PICCOLO PC H 95 G



Sample photo

Order symbol: PC H 95 G
Product nbr: 8724315
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074002273
El. number:
Finland: 3423417
Denmark: 8212001653
Italy: 7201050
Sweden: 2536826
Norway: 2536517

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		170	140	95	Ingress Protection (EN 60529): IP 66/67
inch:		6.7	5.5	3.7	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 746C 5V
Cover screws material:		Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:		Grey			NEMA Class: NEMA 1, 4X, 6, 6P, 12, 13
Gasket material:		Polyurethane			
Temperatures:					Certificates:
Short term:		-40 ... 120 °C			Germanischer Lloyd (GL)
Continuous:		-40 ... 80 °C			Underwriters Laboratories
Short term:		-40 ... 250 °F			Fimko
Continuous:		-40 ... 175 °F			Europe EN 62208: 2003
Accessories:					UL Canada
H-MP		Mounting plate			Gost R
CHM-3		DIN-35 Mounting rail			
DH-3		DIN-35 Mounting rail			
FP 22046		Wall fastening lug (4 pcs)			

