

**FEX FEX 3828 13 T**



Sample photo

**Order symbol:** FEX 3828 13 T  
**Product nbr:** 4120804  
**Description:** Enclosure, PC  
**Remarks:** Ex e II, EN 60079; IK 4J

**EAN:** 6418074008022  
**El. number:**  
 Finland: 3424662  
 Denmark: 8212026476  
 Italy: 7801050  
 Sweden: 4120804  
 Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with silicone gasket and polyamide cover screws.

**Dimensions: Length Width Height Rating:**

<b>mm:</b>	378	278	130	Ingress Protection (EN 60529): IP 54
<b>inch:</b>	14.9	10.9	5.1	Impact Resistance (EN 50014): 4J
				Electrical insulation: Totally insulated
				Halogen free (DIN/VDE 0472, Part 815): Yes

**Materials:**

<b>Material:</b>	Polycarbonate
<b>Base colour:</b>	RAL 7035
<b>Cover colour:</b>	Clear transparent
<b>Cover screws material:</b>	Polyamide
<b>Cover screws colour:</b>	Grey
<b>Gasket material:</b>	Silicone

**Certificates:**

ATEX  
 EC Certificate of Conformity

**Temperatures:**

<b>Short term:</b>	-40 ... 120 °C
<b>Continuous:</b>	-10 ... 80 °C
<b>Short term:</b>	-40 ... 250 °F
<b>Continuous:</b>	14 ... 175 °F

**Accessories:**

EKHVT	Mounting plate
EKJVT	Mounting plate
EKMVT	Mounting plate
EKOVT	Mounting plate
EKPVT	Mounting plate
EKTVT	Mounting plate
EKUVT	Mounting plate
EKV 12	DIN-35 Mounting rail
EKV 22	DIN-35 Mounting rail
EKV 32	DIN-35 Mounting rail

