

FEX FEX 3828 18 G



Sample photo

Order symbol: FEX 3828 18 G
Product nbr: 4130814
Description: Enclosure, PC
Remarks: Ex e II, EN 60079; IK 4J

EAN: 6418074008053
El. number:
 Finland: 3424666
 Denmark: 8212026489
 Italy: 7801155
 Sweden: 4130814
 Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with silicone gasket and polyamide cover screws.

Dimensions: Length Width Height Rating:

mm:	378	278	180	Ingress Protection (EN 60529): IP 54
inch:	14.9	10.9	7.1	Impact Resistance (EN 50014): 4J
				Electrical insulation: Totally insulated
				Halogen free (DIN/VDE 0472, Part 815): Yes

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035
Cover colour:	RAL 7035
Cover screws material:	Polyamide
Cover screws colour:	Grey
Gasket material:	Silicone

Certificates:

ATEX
 EC Certificate of Conformity

Temperatures:

Short term:	-40 ... 120 °C
Continuous:	-10 ... 80 °C
Short term:	-40 ... 250 °F
Continuous:	14 ... 175 °F

Accessories:

EKHVT	Mounting plate
EKJVT	Mounting plate
EKMVT	Mounting plate
EKOVT	Mounting plate
EKPVT	Mounting plate
EKTVT	Mounting plate
EKUVT	Mounting plate
EKV 12	DIN-35 Mounting rail
EKV 22	DIN-35 Mounting rail
EKV 32	DIN-35 Mounting rail

