

CARDMASTER ABS 17/16-L3



Sample photo

Order symbol: ABS 17/16-L3
Product nbr: 7585105
Description: Enclosure, ABS
Remarks: Smoked transparent hinged cover

EAN: 6418074056764
El. number:
 Finland: 3438241
 Denmark: 8212016758
 Sweden: 7585105
 Norway:

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		188	160	106	Ingress Protection (EN 60529): IP 65
inch:		7.4	6.3	4.2	Impact Resistance (EN 62262): IK 07
Materials:					
Material:		ABS			
Base colour:		RAL 7035			
Cover colour:		Smoked grey			
Gasket material:		EPDM and Polyurethane			
Temperatures:					
Short term:		-40 ... 80 °C			
Continuous:		-40 ... 60 °C			
Short term:		-40 ... 175 °F			
Continuous:		-40 ... 140 °F			
Accessories:					
MP 17/16		Mounting plate			
FP 17/16		Front plate (aluminium)			
FC PC 17/16		Frame of PC front plate			
Certificates:					
Gost R					

