



Sample photo

Order symbol: ALX 162609
Product nbr: 7015290
Description: Enclosure, aluminium
Remarks: II 2GD; Ex e IIC Gb; Ex tb IIIC Db IP66

EAN: 6418074009432
El. number:
Finland: 3421825
Denmark: 8212026667
Sweden: 7015290
Norway:

Including: Base, cover with PUR gasket, stainless steel cover screws, with mounting and earth screws and earth terminal.

Dimensions:		Length	Width	Height	Accessories:	
mm:		263	162	91	ARM 0818	DIN-15 Mounting rail
inch:		10.4	6.4	3.6	ARM 0825	DIN-15 Mounting rail
Materials:						
Material:		Aluminium			ARH 12	DIN-35 Mounting rail
Base colour:		RAL 7001			ARH 16	DIN-35 Mounting rail
Cover colour:		RAL 7001			ARH 22	DIN-35 Mounting rail
Cover screws material:		Stainless steel			ARH 26	DIN-35 Mounting rail
Gasket material:		Polyurethane			ARH 36	DIN-35 Mounting rail
					MRS 28540	Wall fastening lug (2 pcs)
					MRS 28541	Wall fastening lug (2 pcs)
Temperatures:						
Short term:		PUR -40 / Si -50 ... 80 °C			Rating:	
Continuous:		PUR -40 / Si -50 ... 80 °C			Ingress Protection (EN 60529): IP 66	
Short term:		PUR -40 / Si -58 ... 175 °F			NEMA Class: NEMA 1, 4, 4X, 6, 12, 13	
Continuous:		PUR -40 / Si -58 ... 175 °F			Certificates:	
Accessories:						
AM 0808		Mounting plate				
AM 0813		Mounting plate				
AM 0818		Mounting plate				
AM 0825		Mounting plate				
AM 1212		Mounting plate				
AM 1222		Mounting plate				
AM 1236		Mounting plate				
AM 1616		Mounting plate				
AM 1626		Mounting plate				
ARM 0610		DIN-15 Mounting rail				
ARM 0615		DIN-15 Mounting rail				
ARM 0808		DIN-15 Mounting rail				
ARM 0813		DIN-15 Mounting rail				

ALU 263x162x91

