

CAB CAB PC 302018 T



Sample photo

Order symbol: CAB PC 302018 T
Product nbr: 8113030
Description: Cabinet, PC
Remarks: Latches on the long side

EAN: 6418074020017
El. number:
Finland: 3424151
Denmark: 8212020210
Italy: 7822015
Sweden: 2539935
Norway:

Including: Cabinet base, door with EPDM gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:			Length	Width	Height	Rating:
mm:	300	200	180			Ingress Protection (EN 60529): IP 65
inch:	11.8	7.9	7.1			Impact Resistance (EN 62262): IK 08
Materials:						Electrical insulation: Totally insulated
Material:	Polycarbonate					Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:	RAL 7035					UV resistance: UL 508
Cover colour:	Smoked grey					Flammability Rating (UL 746 C 5): UL 746C 5V
Gasket material:	EPDM					Glow Wire Test (IEC 695-2-1) °C: 960
Temperatures:						UL Type: UL TYPE 1, 4, 4X, 12, 13
Short term:	-40 ... 120 °C					Certificates:
Continuous:	-40 ... 80 °C					
Short term:	-40 ... 250 °F					
Continuous:	-40 ... 175 °F					
Accessories:						Germanischer Lloyd (GL)
EKIV 23	Mounting plate					Underwriters Laboratories
EKIV 17	DIN-35 Mounting rail					Fimko
DS35170E1	DIN-35 Mounting rail					Lloyds Register of Shipping (LR)
EKIV 27	DIN-35 Mounting rail					Europe EN 62208: 2003
DS35270E1	DIN-35 Mounting rail					UL Canada
FP A 23	Swing-out door/Front plate					Gost R
MB 12225 AL	Swing door set					
FP 23	Front plate					
FP 12-23	Front plate					
DRF 23	DIN rail frame set					

