

CAB CAB PC 303018 T3B



Sample photo

Order symbol: CAB PC 303018 T3B
Product nbr: 8113042
Description: Cabinet, PC
Remarks: Lock on the long side

EAN: 6418074020154
El. number:
 Finland: 3424161
 Denmark: 8212019234
 Italy: 7822030
 Sweden: 2539943
 Norway:

Including: Cabinet base, door with EPDM gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:		Length	Width	Height	Rating:
mm:		300	300	180	Ingress Protection (EN 60529): IP 65
inch:		11.8	11.8	7.1	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		Smoked grey			Flammability Rating (UL 746 C 5): UL 746C 5V
Gasket material:		EPDM			Glow Wire Test (IEC 695-2-1) °C: 960
Temperatures:					UL Type: UL TYPE 1, 4, 4X, 12, 13
Short term:		-40 ... 120 °C			Certificates:
Continuous:		-40 ... 80 °C			Germanischer Lloyd (GL)
Short term:		-40 ... 250 °F			Underwriters Laboratories
Continuous:		-40 ... 175 °F			Fimko
Accessories:					Lloyds Register of Shipping (LR)
EKIV 33		Mounting plate			Europe EN 62208: 2003
EKIV 27		DIN-35 Mounting rail			UL Canada
DS35270E1		DIN-35 Mounting rail			Gost R
FP A 33		Swing-out door/Front plate			
MB12225 AL		Swing door set			
FP 33		Front plate			
FP 12-33		Front plate			
FP 12x2-33		Front plate			
DRF 33		DIN rail frame set			

