

CARDMASTER PC 21/18-3



Order symbol: PC 21/18-3
Product nbr: 7525154
Description: Enclosure, PC
Remarks: Smoked transparent hinged cover

EAN: 6418074056733
El. number:
 Finland: 3438231
 Denmark: 8212016664
 Sweden: 2537306
 Norway: 2536926

Including: Base, terminal compartment cover with PUR gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Sample photo

Dimensions:		Length	Width	Height	Rating:
mm:		235	185	119	Ingress Protection (EN 60529): IP 65
inch:		9.3	7.3	4.7	Impact Resistance (EN 62262): IK 08/07
Materials:					
Material:		Polycarbonate			Electrical insulation: Totally insulated
Base colour:		RAL 7035			Halogen free (DIN/VDE 0472, Part 815): Yes
Cover colour:		Smoked grey			UV resistance: UL 508
Gasket material:		EPDM and Polyurethane			Flammability Rating (UL 746 C 5): UL 746C 5V
Temperatures:					
Short term:		-40 ... 120 °C			Glow Wire Test (IEC 695-2-1) °C: 960
Continuous:		-40 ... 80 °C			NEMA Class: NEMA 1, 3, 3R, 4X, 12, 13
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Certificates:					
Underwriters Laboratories					
Fimko					
Europe EN 62208: 2003					
UL Canada					
Gost R					
Accessories:					
MP 21/18		Mounting plate			
FP 21/18		Front plate (aluminium)			
FC PC 21/18		Frame of PC front plate			

CARDMASTER 213x185x90-119

