

**CARDMASTER ABS 36/31-3**



**Order symbol:** ABS 36/31-3  
**Product nbr:** 7585020  
**Description:** Enclosure, ABS  
**Remarks:** Smoked transparent hinged cover

**EAN:** 6418074056801  
**El. number:**  
 Finland: 3438246  
 Denmark: 8212016787  
 Sweden: 7585020  
 Norway:

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Sample photo

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		390	316	167	Ingress Protection (EN 60529): IP 65
<b>inch:</b>		15.4	12.4	6.6	Impact Resistance (EN 62262): IK 07
<b>Materials:</b>					
<b>Material:</b>		ABS			
<b>Base colour:</b>		RAL 7035			
<b>Cover colour:</b>		Smoked grey			
<b>Gasket material:</b>		EPDM and Polyurethane			
<b>Temperatures:</b>					
<b>Short term:</b>		-40 ... 80 °C			
<b>Continuous:</b>		-40 ... 60 °C			
<b>Short term:</b>		-40 ... 175 °F			
<b>Continuous:</b>		-40 ... 140 °F			
<b>Accessories:</b>					
MP 36/31		Mounting plate			
FP 36/31		Front plate (aluminium)			
<b>Certificates:</b>					
Gost R					

