

**CAB CAB ABS 604022 T3B**



Sample photo

**Order symbol:** CAB ABS 604022 T3B  
**Product nbr:** 8183072  
**Description:** Cabinet, ABS  
**Remarks:** Locks on the long side

**EAN:** 6418074020512  
**El. number:**  
 Finland: 3424378  
 Denmark: 8212019098  
 Italy: 7812070  
 Sweden: 2540055  
 Norway:

Including: Cabinet base, door with EPDM gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

| Dimensions:             |  | Length                     | Width | Height | Rating:                                    |
|-------------------------|--|----------------------------|-------|--------|--|
| <b>mm:</b>              |  | 600                        | 400   | 220    | Ingress Protection (EN 60529): IP 65       |
| <b>inch:</b>            |  | 23.6                       | 15.7  | 8.7    | Impact Resistance (EN 62262): IK 08        |
| <b>Materials:</b>       |  |                            |       |        | Electrical insulation: Totally insulated   |
| <b>Material:</b>        |  | ABS                        |       |        | Halogen free (DIN/VDE 0472, Part 815): Yes |
| <b>Base colour:</b>     |  | RAL 7035                   |       |        | Flammability Rating (UL 746 C 5): UL 94 HB |
| <b>Cover colour:</b>    |  | Smoked grey                |       |        | Glow Wire Test (IEC 695-2-1) °C: 650       |
| <b>Gasket material:</b> |  | EPDM                       |       |        | NEMA Class: NEMA 1, 4, 4X, 12, 13          |
| <b>Temperatures:</b>    |  |                            |       |        | <b>Certificates:</b>                       |
| <b>Short term:</b>      |  | -40 ... 80 °C              |       |        | Fimko                                      |
| <b>Continuous:</b>      |  | -40 ... 60 °C              |       |        | Europe EN 62208: 2003                      |
| <b>Short term:</b>      |  | -40 ... 175 °F             |       |        | Gost R                                     |
| <b>Continuous:</b>      |  | -40 ... 140 °F             |       |        |  |
| <b>Accessories:</b>     |  |                            |       |        |  |
| EKIV 64H                |  | Mounting plate             |       |        |  |
| EKIV 37                 |  | DIN-35 Mounting rail       |       |        |  |
| DS35370E1               |  | DIN-35 Mounting rail       |       |        |  |
| FP A 64                 |  | Swing-out door/Front plate |       |        |  |
| MB 12225 AL             |  | Swing door set             |       |        |  |
| FP 64                   |  | Front plate                |       |        |  |
| FP 18x3-64              |  | Front plate                |       |        |  |
| DRF 63/64               |  | DIN rail frame set         |       |        |  |

