

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **39-01-2240**
Status: **Active**
Overview: Mini-Fit Jr.™
Description: 4.20mm Pitch Mini-Fit Jr.™ Receptacle Housing, Dual Row, UL 94V-2, 24 Circuits

Documents:

3D Model	Product Specification PS-5556-001 (PDF)
Drawing (PDF)	Test Summary TS-5556-002 (PDF)
Product Specification PS-45750-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	<u>5557</u>
Application	Power, Wire-to-Wire
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with <u>45750</u> series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current derating information.. Glow Wire Equivalent Part
MolexKits	Yes
Overview	<u>Mini-Fit Jr.™</u>
Product Name	Mini-Fit Jr.™
UPC	800753584051

Physical

Breakaway	No
Circuits (maximum)	24
Color - Resin	Natural
Flammability	94V-2
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Nylon
Net Weight	4701.100/mg
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Electrical

Current - Maximum per Contact	13A
-------------------------------	-----

Material Info

Old Part Number	5557-24R
-----------------	----------

Reference - Drawing Numbers

Product Specification	PS-45750-001, PS-5556-001
Sales Drawing	SD-5557-003
Test Summary	TS-5556-002



EU RoHS

ELV and RoHS Compliant

REACH SVHC Contains SVHC: No Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

5557Series

Mates With

5559 Dual Row, 5566 Vertical with Pegs, 5566 Vertical without Pegs, 5569 Right Angle Dual Row with Flanges, 5569 Right Angle Dual Row with Pegs, 43810 , 44068 , 44281 , 87427 , 42404 , 42440

Use With

5556 Mini-Fit® Female Crimp Terminals

This document was generated on 05/15/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION