

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [16-02-0102](#)
Status: **Active**
Overview: [C-Grid® Products](#)
Description: SL™ Crimp Terminal, Series 70058, Female, with Tin (Sn) Plated Contact, 22-24 AWG, Bag

Documents:

[Drawing \(PDF\)](#) [Test Summary TS-70058-001 \(PDF\)](#)
[Product Specification PS-70058 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-70400 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	70058
Application	Signal
Crimp Quality Equipment	Yes
Overview	C-Grid® Products
Packaging Alternative	16-02-0086 (Reel)
Product Name	SL™
UPC	800753595637

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.071/g
Packaging Type	Bag
Plating min - Mating	3.810µm
Plating min - Termination	1.905µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.63mm max.
Wire Size AWG	22, 24
Wire Size mm²	N/A

Material Info

Old Part Number 70058-0222

Reference - Drawing Numbers

Product Specification	PS-70058, PS-70400
Sales Drawing	SD-70058-0222
Test Summary	TS-70058-001



image - Reference only

EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[70058Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool	0011030036
Insertion Tool	0011020022
Hand Crimp Tool	0638118700

Japan

Description	Product #
Hand Crimp Tool	0570365000
Hand Crimp Tool	0570375000