


CABLE NO. : 4101020100
(3070100014-07)




接线图(1)


说明:

1. 产品购买同批累计线材达到1500米时, 用3070100022的线和接线图(1);
2. 产品购买同批累计线材不能达到1500米时, 用3070700014的线替代, 但白色芯线不用.

MICROPHONE CABLE



CABLE NO. : 4101010040
(3070100022-07)



S.R 宁波日鼎电子科技有限公司

DIMENSIONS ARE IN MILLIMETERS (默认单位:mm) UNLESS OTHERWISE SPECIFIED TOLERANCES (一般公差) 0.5~6 = \pm 0.2 > 6~30 = \pm 0.4 > 30~120 = \pm 0.6 > 120~315 = \pm 1 > 315~1000 = \pm 1.6 ANGLES(角度) = \pm 5°	品号	5113070032	图类	装配图	
	品名	SVP573-6-PT-NL	角法		
	制图	王英	2010.11.19	比例	
	核对	程志	2010.11.19	版本	A4
	核准	徐意	2010.11.22	图号	5113070032_SVP573-6-PT-NL_CAD01A4