




Cable Word:

E309675 9\ AWM 2919 80°C 30V VW-1 C 9\ AWM A I/II 80°C 30V FT1 LOW VOLTAGE COMPUTER CABLE HOE

TOLERANCE	SIGNATURES	DATE
0 - 10 ±0.05	DRAFT: ZHOU XIN GUO	15-03-2012
10 - 99 ±0.5	CHECKED: XU FU YOU	
100 - 999 ±10.0		
1000 - 9999 ±100.00		
10000 - 99999 ±1000.00		

REV.	PART NO. & SAMPLE NO.	BY	APPROVAL:	SCALE	UNIT	REV.	TITLE	CUSTOMER
A				1:1	mm	∅	SVGA Cable HDDB15M-5*BNC Plugs (5 Coaxial UL 2919, W/Ferrite Core)	
B								