



<b>Notification</b>	
<b>Product Code</b>	NLKVS-534A
<b>Short Description</b>	4 Port VGA Splitter, 450Mhz, up to 65Mtr
<b>Full Description</b>	<p>The NLKVS-range of Video Splitters are designed for desktop use, supplied in a durable, compact metal housing. The splitters duplicate and boost the input signal to 2, 4 or 8 VGA, SVGA or Multi-sync Monitors, with a signal rate of <b>450 Mhz</b>. Video Splitters are ideal for applications such as tradeshow, business meetings and demonstrations.</p> <p>These products are independent of software and other than cables and Monitors, no additional hardware is required.</p>
<b>Extra Information</b>	<p><b>Specification</b>                  250 - 450Mhz Video Bandwidth                  4 Port                  Supports up to 2048 x 1536 Resolution                  Supports DDC, DDC2 &amp; DDC2B(Port 1 only)                  Duplicate one signal input to multiple outputs                  Ability to be cascaded                  Effective transmission distance: 65 Mtrs                  Power saving mode                  Metal Case</p> <p><b>Contents</b>                  1 x Video Splitter                  1 x Power Supply                  1 x User Manual</p>